

Miniature cutting insert, type AF HC5640 for axial recessing

ATORN®

Application

For axial recessing in the material groups of steel and (stainless steel) with low to high cutting speeds and medium cutting conditions.

Version

- solid carbide cutting insert with inner cooling

Advantage

- tough cemented carbide type for broad application field
- sturdy geometry for axial cutter insert
- ideal for use with inefficient machines and unstable cutting conditions



Art. No.	17131 104
Shaft diameter	4 mm
ISO name	AF
Length	51 mm
Clearance length	15 mm
Recessing width	1 mm
Plunge depth	1.5 mm
Programming size	1.95 mm
Min. bore diameter	5 mm
Machining direction	Right
Carbide type	HC5640
Material to be processed	Steel, Stainless steel, Non-ferrous metal, Cast metal

EAN-Code

4050293267068