

## Hydraulic expansion chuck

In accordance with ISO 12164 (DIN 69893)



### Application:

For clamping drill bits and milling tools with straight shank.

### Execution:

- Longer service life of cutting tools.
- Capable of clamping all common shank types.
- With axial length adjustment (max. V in the drawing).

### Advantage:

- High-precision centric clamping.
- High torque transfer.
- Good surface qualities.
- Suitable for high rotation speeds.
- Excellent vibration-damping properties.

### Delivery:

1x hydraulic expansion chuck in accordance with ISO 12164 (DIN 69893).



<b>Art. no.</b>	<b>23735 053</b>
<b>Brand</b>	SCHUNK
<b>Manufacturer Part Number</b>	0204054
<b>Tool holding device</b>	HSK 63
<b>Construction length</b>	Slim
<b>Clamping diameter</b>	12 mm
<b>Form</b>	A
<b>Projecting length</b>	85 mm
<b>Tapered diameter</b>	32 mm
<b>Outer diameter</b>	50 mm
<b>Clear length</b>	40 mm
<b>Clamp in depth</b>	46 mm
<b>Suitable for thread</b>	M10 x 1
<b>Max. adjustment travel</b>	10 mm
<b>Coolant supply</b>	Internal axial
<b>Balancing quality</b>	G 2.5 at 25 rpm
<b>Gross Weight</b>	1.111 kg
<b>Product Group</b>	229