

## General Information

Extended Product Type:	CAL4-11
Product ID:	1ISBN010120R1011
EAN:	3471523130043
Catalog Description:	CAL4-11 Auxiliary Contact Block
Long Description:	CAL4-11 Auxiliary Contact Block

## Categories

Products » Low Voltage Products and Systems » Control Products » Contactors » Block Contactors Accessories

## Ordering

EAN:	3471523130043
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85389099

## Dimensions

Product Net Weight:	0.040 kg
---------------------	----------

## Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	125 mm
Package Level 1 Height:	20 mm
Package Level 1 Length:	125 mm
Package Level 1 Gross Weight:	0.04 kg
Package Level 1 EAN:	3471523130043
Package Level 2 Units:	300 piece
Package Level 3 Units:	5400 piece
Product Packing Type:	Bag

## Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2008 Q1
--------------	---

## Technical UL/CSA

Tightening Torque UL/CSA:	Auxiliary Circuit 11 in·lb
---------------------------	----------------------------

## Additional Information

Connecting Capacity Auxiliary Circuit:	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm <sup>2</sup> Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm <sup>2</sup> Flexible with Insulated Ferrule 2x 0.75 ... 1.5 mm <sup>2</sup> Rigid 1/2x 1...2.5 mm <sup>2</sup>
Conventional Free-air Thermal Current (I <sub>th</sub> ):	acc. to IEC 60947-5-1, q = 40 °C 16 A
IIT Publishing Status:	Level 0 - Information enabled
Maximum Electrical Switching Frequency:	AC-15 1200 cycles per hour DC-13 900 cycles per hour
Maximum Mechanical Switching Frequency:	3600 cycles per hour
Mounted Auxiliary Contacts:	1 NO, 1 NC
Number of Auxiliary Contacts NC:	1
Number of Auxiliary Contacts NO:	1
Product Main Type:	Accessories for Block Contactors
Product Name:	Auxiliary Contact Block
Rated Frequency (f):	Auxiliary Circuit 50 / 60 Hz
Rated Impulse Withstand Voltage (U <sub>imp</sub> ):	6 kV
Rated Insulation Voltage (U <sub>i</sub> ):	acc. to UL/CSA 600 V acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V
Rated Operational Current AC-15 (I <sub>e</sub> ):	(220 / 240 V) 4 A (24 / 127 V) 6 A (400 / 440 V) 3 A (500 V) 2 A (690 V) 2 A
Rated Operational Current DC-13	(110 V) 0.55 A / 60 W (125 V) 0.55 A / 69 W

<b>(I<sub>e</sub>):</b>	(220 V) 0.27 A / 60 W
	(24 V) 6 A / 144 W
	(250 V) 0.27 A / 68 W
	(400 V) 0.15 A / 60 W
	(48 V) 2.8 A / 134 W
	(500 V) 0.13 A / 65 W
	(600 V) 0.1 A / 60 W
(72 V) 1 A / 72 W	

**Rated Operational Voltage:** Auxiliary Circuit 24 ... 690 V

**Rated Short-time Withstand Current (I<sub>cw</sub>):** for 0.1 s 140 A  
for 1 s 100 A

**RoHS Date:** 20090609

**Suitable For:** AF09  
AF12  
AF16  
AF26  
AF30  
AF38  
AF40  
AF52  
AF65  
AF80  
AF96  
NF

**Terminal Type:** Screw Terminals

**Tightening Torque:** Auxiliary Circuit 1.2 N·m

**Wire Stripping Length:** Auxiliary Circuit 10 mm

### Certificates and Declarations (Document Number)

**ABS Certificate:** ABS\_15-GE1349500-PDA\_90682247

**CB Certificate:** CB\_SE\_70921

**CCC Certificate:** CCC\_2011010304496319

**Data Sheet, Technical Information:** 1SBC100173C0201

**Declaration of Conformity - CE:** 1SBD250007U1000

**EAC Certificate:** EAC\_RU C-FR ME77 B01048

**GOST Certificate:** GOST\_POCCFR.ME77.B07175.pdf

**LR Certificate:** LRS\_1300087E1

**RINA Certificate:** RINA\_ELE084013XG

**RMRS Certificate:** RMRS\_1300133124

**RoHS Information:** 1SBD251010E1000

**UL Certificate:** UL\_20091128-E252354-3-1

### Classifications

**E-number:** 3211435

**ETIM 4:** EC002498 - Accessories for low-voltage switch technology

**ETIM 5:** EC002498 - Accessories for low-voltage switch technology

**ETIM 6:** EC002498 - Accessories for low-voltage switch technology

**Object Classification Code:** K

**UNSPSC:** 39121500

