

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0763527001](#)
Status: **Active**
Overview: SFP+ and SFP Interconnect Solutions
Description: Small Form-factor Pluggable Plus (SFP+) Stacked 2-by-8 Multi-Port Connector with Inner Ports and Outer Lite Pipe Ports, with Improved EMI Metal Gasket, 320 Circuits, Tin (Sn) Tails

Documents:

3D Model	Application Specification AS-76090-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-76352-001-001 (PDF)
Product Specification PS-75310-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-75310-001-001 (PDF)	

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	I/O Connectors
Series	76352
Application	Module-to-Board
Component Type	Receptacle
Electrical Model	Yes
Overview	SFP+ and SFP Interconnect Solutions
Product Name	SFP Plus
Type	N/A
UPC	884982411821

Physical

Boot Color	N/A
Circuits (Loaded)	320
Circuits (maximum)	320
Circuits Detail	320
Durability (mating cycles max)	100
Flammability	94V-0
Gender	Female
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic, Polycarbonate
Net Weight	185.128/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	2.07mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[76352 Series](#)

Ports	16
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Through Hole - Compliant Pin
Waterproof / Dustproof	No

Electrical

Current - Maximum per Contact	0.5A
Grounding to Panel	None
Shield Type	EMI Gasket
Shielded	Yes
Voltage - Maximum	120V AC (RMS)/DC

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info**Reference - Drawing Numbers**

Application Specification	AS-75310-001-001, AS-76090-001-001
Electrical Model Document	EE-76090-001
Packaging Specification	PK-76352-001-001
Product Specification	PS-75310-001
S-Parameter Model	SP-76090-001
Sales Drawing	SD-76352-0002-001

This document was generated on 05/15/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION