### **Ultra Fast Recovery High Efficiency Rectifier Diodes** VRRM - 50 Volts to 1000 Volts, 2A





### **Features**


- Glass Passivated (GPP)
- Low cost
- Ultra fast switching for high efficiency
- · Low reverse leakage current
- Low forward voltage drop
- High current capability
- The plastic material carries UL recognition 94V-0
- Case style: DO-204-AC (DO-15) molded plastic

### Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

## RoHS **Compliant**

DO-204-AC (DO-15)



Dimensions: Inches (Millimetres)

Characteristics	Symbol	MP000939	MP000940	MP000941	MP000942	MP000943	MP000944	MP000945	MP000946	Unit
Maximum Repetitive Peak Reverse Voltage	VRRM	50	100	200	300	400	600	800	1000	
Maximum RMS Voltage	VRMS	35	70	140	210	280	420	560	700	V
Maximum DC Blocking Voltage	VDC	50	100	200	300	400	600	800	1000	
Maximum Average Forward Rectified Current @ T <sub>A</sub> = 50°C	I(AV)	2						А		
Peak Forward Surge Current, 8.3mS Single Half Sine-Wave, Superimposed on Rated Load (JEDEC Method)	Іғѕм	60							А	
Peak Forward Voltage at 2A DC	VF	1 1.3				1.7		V		
Maximum DC Reverse Current at Rated @ TJ = 25°C DC Blocking Voltage @ TJ = 100°C	lr	5 100						μА		
Maximum Reverse Recovery Time (Note 1)	Trr	50 75							nS	
Typical Junction Capacitance (Note2)	Сı	50 30						pF		

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands





Characteristics	Symbol	MP000939	MP000940	MP000941	MP000942	MP000943	MP000944	MP000945	MP000946	Unit
Typical Thermal Resistance Junction to Ambient	Rеja	25							°C/ W	
Operating Junction Temperature Range	TJ	-55 to +150						°C		
Storage Temperature Range	Тѕтс	-55 to +150						°C		

#### Notes:

- 1. Measured with  $I_F = 0.5A$ ,  $I_R = 1A$ ,  $I_{RR} = 0.25A$
- 2. Measured at 1MHz and applied reverse voltage of 4V DC.
- 3. The typical data above is for reference only.

### **Rating and Characteristic Curves**




Fig. 3 - Typical Junction Capacitance




Fig. 2 - Maximum Non-Repetitive Surge Current





Fig. 4 - Typical Forward Characteristics




Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands



# Ultra Fast Recovery High Efficiency Rectifier Diodes VRRM - 50 Volts to 1000 Volts, 2A




Fig. 5 - Typical Forward Characteristics



Instantaneous Forward Current (A)

Fig. 6 - Typical Forward Characteristics



### **Part Number Table**

Description	Part Number	
Rectifier Diode, Ultra Fast, 50V, 2A, DO-204AC (DO-15)	MP000939	
Rectifier Diode, Ultra Fast, 100V, 2A, DO-204AC (DO-15)	MP000940	
Rectifier Diode, Ultra Fast, 200V, 2A, DO-204AC (DO-15)	MP000941	
Rectifier Diode, Ultra Fast, 300V, 2A, DO-204AC (DO-15)	MP000942	
Rectifier Diode, Ultra Fast, 400V, 2A, DO-204AC (DO-15)	MP000943	
Rectifier Diode, Ultra Fast, 600V, 2A, DO-204AC (DO-15)	MP000944	
Rectifier Diode, Ultra Fast, 800V, 2A, DO-204AC (DO-15)	MP000945	
Rectifier Diode, Ultra Fast, 1kV, 2A, DO-204AC (DO-15)	MP000946	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

