

## DIAPOINT single-diamond dressing tools with 3-5 natural points, few impurities (2nd. quality)

For dressing ceramic grinding wheels




### Application:

Suitable for all machines with corresponding holder. **Chucking:** Inclination of dressing tool to sanding disc centre from 5° to 15° required. We recommend **selecting the appropriate diamond weight** for individual diamond dressing tools according to the following diagram depending on the sanding disc to be adjusted.

### Version:

- Universal, traditional dressing tool with a single diamond with protruding working tip



<b>Art. no.</b>	<b>61135 040</b>
<b>Shank style</b>	Morse taper
<b>Morse taper size</b>	MK 0
<b>Natural tip quality</b>	2
<b>Weight of diamond</b>	0.4 carat
<b>Min./max. side feed per revolution</b>	0.05-0.15 m/s
<b>Min./max supply per throughput</b>	0.01-0.03 mm
<b>Number of pieces per packet</b>	1 PCS
<b>DIN</b>	228