

SDUC offset solid carbide boring bar, positive, right

for longitudinal and copy turning using DC indexable insert

ATORN[®]

Application

For longitudinal and copy turning with DC 55° indexable insert.

Version

- precision-manufactured **solid carbide** boring bar, with inner cooling, D type, 93.5° pitch angle, 55° tip angle, 7° clearance angle

Advantage

- Very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces
- Extremely high rigidity and cutting quality



Art. No.	17847 238
ISO name	E08K-SDUC R/L 07
Min. bore diameter	13.5 mm
Shaft diameter	8 mm
Cutting edge height	3.5 mm
Clearance length	10 mm
Length	125 mm
Clamping surface height	7 mm
Programming size	7.5 mm
Suitable for indexable inserts	DC.. 0702..
Tool design	Right
DIN	8024

EAN-Code

4050293344233