

Lever gauge

MarTest



Application:

For measuring deviations in concentricity, axial run-out, parallelism and flatness. For centring shafts, boreholes and aligning workpieces.

Execution:

- Impact-resistant movement
- Dial sealed with O-ring
- Anti-magnetic components
- Automatic switching of callipers direction
- Measuring element supported in 8 precious stones
- 3 dovetail mounting surfaces

Advantage:

- Viewing window made of mineral glass, therefore resistant to solvents



Art. no.	33303 070
Brand	MAHR
Manufacturer Part Number	4306200
Length measuring range	0.5 mm
Scale value	0.01 mm
Measurement force	0.07 N
Length of measuring sensor from centre of ball	41.3 mm
Material of measuring ball	Carbide
Ball diameter	2 mm
Pivot range of measuring sensor	220 Degree
Diameter	28 mm
Connection thread	M2
DIN	2270
Calibration Group	L
Gross Weight	0.155 kg
Product Group	305

EAN

4059192013523