



Part no.: 50114185
REF 6-S-20x40
Reflector



Figure can vary

Contents

- Technical data
- Dimensioned drawings

Part no.: 50114185 – REF 6-S-20x40 – Reflector

Technical data

Mechanical data	
Design	Rectangular
Mounting dimension, width	20 mm
Reflection surface width	16 mm
Mounting dimension, height	60 mm
Reflection surface height	38 mm
Mounting dimension, thickness	6 mm
Direction independent	No
Triple reflector size	0.3 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Mikrotriple
Net weight	6 g
Type of fastening	Screw type

Environmental data	
Ambient temperature, operation	-40 ... 70 °C

Certifications	
Degree of protection	IP 67

Classification	
Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467

Dimensioned drawings

All dimensions in millimeters

