## Connection Socket M12 × 1; 8-pin

## BG80-ME


Part Number




## **Technical Data**

Mechanical Data			
Connection 1	Socket, straight		
Connection mode 1	M12 × 1, 8-pin M12: 0,6 Nm 48 mm		
Torque			
Cable Diameter			
Wire cross-section	≤ 0,5 mm²		
Assembling	Screw Terminal Technology IP67 -2590 °C		
Degree of Protection			
Temperature Range			
Material Sleeve Nut	CuZn, nickel-plated		
Packaging unit	1 Piece		
Connection Diagram No.	S47		
Connection Equipment No.	80		

## • Socket M12 × 1, straight





Leger	nd	PT	Platinum measuring resistor	ENAR5422	Encoder A/Ā (TTL)
+	Supply Voltage +	пс	not connected	ENBRS422	Encoder B/B (TTL)
-	Supply Voltage 0 V	U	Test Input	ENA	Encoder A
~	Supply Voltage (AC Voltage)	Ū	Test Input inverted	ENB	Encoder B
Α	Switching Output (NO)	W	Trigger Input	Amin	Digital output MIN
Ā	Switching Output (NC)	W-	Ground for the Trigger Input	Амах	Digital output MAX
V	Contamination/Error Output (NO)	0	Analog Output	Аок	Digital output OK
⊽	Contamination/Error Output (NC)	0-	Ground for the Analog Output	SY In	Synchronization In
E	Input (analog or digital)	BZ	Block Discharge	SY OUT	Synchronization OUT
Т	Teach Input	Awv	Valve Output	OLT	Brightness output
Z	Time Delay (activation)	а	Valve Control Output +	М	Maintenance
S	Shielding	b	Valve Control Output 0 V	rsv	reserved
RxD	Interface Receive Path	SY	Synchronization	Wire Colors according to DIN IEC 757	
TxD	Interface Send Path	SY-	Ground for the Synchronization	ВК	Black
RDY	Ready	E+	Receiver-Line	BN	Brown
GND	Ground	S+	Emitter-Line	RD	Red
CL	Clock	÷	Grounding	OG	Orange
E/A	Output/Input programmable	SnR	Switching Distance Reduction	YE	Yellow
•	IO-Link	Rx+/-	Ethernet Receive Path	GN	Green
PoE	Power over Ethernet	Tx+/-	Ethernet Send Path	BU	Blue
IN	Safety Input	Bus	Interfaces-Bus A(+)/B(-)	VT	Violet
OSSD	Safety Output	La	Emitted Light disengageable	GY	Grey
Signal	Signal Output	Mag	Magnet activation	WH	White
BI_D+/-	Ethernet Gigabit bidirect, data line (A-D)	RES	Input confirmation		Pink
ENORS	2 Encoder 0-pulse 0-0 (TTL)	EDM	Contactor Monitoring	GNYE	Green/Yellow