## RPM41BD

# Power plug-in relay, 15 A, 4 CO, 24 V DC





#### Main

| Range of product                             | Harmony Relay             |
|--|---------------------------|
| Series name                                  | Power                     |
| Product or component type                    | Plug-in relay             |
| Device short name                            | RPM                       |
| Contacts type and composition                | 4 C/O                     |
| [Uc] control circuit voltage                 | 24 V DC                   |
| [Ithe] conventional enclosed thermal current | 15 A -40131 °F (-4055 °C) |
| Status LED                                   | Without                   |
| Control type                                 | Lockable test button      |
| Utilisation coefficient                      | 20 %                      |

#### Complementary

| Complementary                          |   |
|--|---|
| Shape of pin                           | Flat                                      |
| [Ui] rated insulation voltage          | 250 V conforming to IEC                   |
|  | 300 V CSA                                 |
|  | 300 V UL                                  |
| [Uimp] rated impulse withstand voltage | 4 kV 1.2/50 μs                            |
| Contacts material                      | AgNi                                      |
| [le] rated operational current         | 15 A 277 V AC) UL                         |
|  | 15 A 28 V DC) UL<br>15 A 250 V AC) NO IEC |
|  | 15 A 28 V DC) NO IEC                      |
|  | 7.5 A 250 V AC) NC IEC                    |
|  | 7.5 A 28 V DC) NC IEC                     |
| Maximum switching voltage              | 250 V IEC                                 |
| Resistive load current                 | 15 A 250 V AC                             |
|  | 15 A 28 V DC                              |
| Maximum switching capacity             | 3750 VA                                   |
|  | 420 W                                     |
| Minimum switching capacity             | 170 mW 10 mA, 17 V                        |
| Operating rate                         | <= 1200 cycles/hour under load            |
|  | <= 18000 cycles/hour no-load              |
| Mechanical durability                  | 10000000 cycles                           |
| Electrical durability                  | 100000 cycles for resistive load          |
| Average coil consumption               | 1.6 W                                     |
| Drop-out voltage threshold             | >= 0.1 Uc DC                              |
| Operate time                           | 20 ms at nominal voltage                  |
| Release time                           | 20 ms at nominal voltage                  |
| Average coil resistance                | 303 Ohm 68 °F (20 °C) +/- 10 %            |
| Rated operational voltage limits       | 19.226.4 V DC                             |
| Protection category                    | RTI                                       |
| Test levels                            | Level A group mounting                    |
| Operating position                     | Any position                              |
| Pollution degree                       | 3   |
| Safety reliability data                | B10d = 100000                             |
| Net Weight                             | 0.16 lb(US) (0.071 kg)                    |
| Device presentation                    | Complete product                          |

| _  |    |     |    |   |   |   |    |
|----|----|-----|----|---|---|---|----|
| ь. | n۱ | /Ir | `` | n | m | Δ | ni |
|    |    |     |    |   |   |   |    |

| Dielectric strength                   | 1500 V AC between contacts micro disconnection<br>2000 V AC between coil and contact reinforced<br>2000 V AC between poles basic |  |
|---------------------------------------|--|--|
| Standards                             | EN/IEC 61810-1<br>CSA C22.2 No 14<br>UL 508  |  |
| Product certifications                | EAC<br>CSA<br>RoHS<br>UL   |  |
| Ambient air temperature for storage   | -40185 °F (-4085 °C)   |  |
| Ambient air temperature for operation | -4055 °C   |  |
| Vibration resistance                  | 3 gn +/- 1 mm 10150 Hz)5 cycles in operation 5 gn +/- 1 mm 10150 Hz)5 cycles not operating                                       |  |
| Degree of protection (Housing only)   | IP40 conforming to EN/IEC 60529  |  |
| Shock resistance                      | 15 gnin operation 30 gnnot operating   |  |

#### Ordering and shipping details

| Category              | 21127 - ZELIO ICE CUBE RELAYS |
|-----------------------|-------------------------------|
| Discount Schedule     | CP2                           |
| GTIN                  | 00785901572848                |
| Nbr. of units in pkg. | 10                            |
| Package weight(Lbs)   | 0.15 lb(US) (0.07 kg)         |
| Returnability         | Yes                           |
| Country of origin     | CN                            |
|                       |                               |

## Packing Units

| Package 1 Height | 0.470 dm |  |
|------------------|----------|--|
| Package 1 width  | 0.400 dm |  |
| Package 1 Length | 0.280 dm |  |

#### Offer Sustainability


| Sustainable offer status   | Green Premium product  |
|----------------------------|--|
| California proposition 65  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACh Regulation           | REACh Declaration  |
| REACh free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)   |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| RoHS exemption information | €Yes   |
| China RoHS Regulation      | ☑ China RoHS Declaration   |
| Environmental Disclosure   | Product Environmental Profile  |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.   |

#### Contractual warranty


| Warranty | 18 months |  |
|----------|-----------|--|

# RPM41BD


#### **Dimensions**




Pin Side View



#### Wiring Diagram





Symbols shown in blue correspond to Nema marking.


# Product data sheet Performance Curves

## RPM41BD

#### **Electrical Durability of Contacts**

Durability (inductive load) = durability (resistive load) x reduction coefficient.


Resistive AC load



X Switching capacity (kVA)


Y Durability (Number of operating cycles)

Reduction coefficient for inductive AC load (depending on power factor cos φ)



Y Reduction coefficient (A)

Maximum switching capacity on resistive DC load



X Voltage DCY Current DC

Note: These are typical curves, actual durability depends on load, environment, duty cycle, etc.