

BLINDNIETE


FLACHRUNDKOPF (~ DIN EN ISO 15979)

BLIND RIVETS

DOMED HEAD (~ DIN EN ISO 15979)


RIVETS AVEUGLES

TÊTE PLATE (~ DIN EN ISO 15979)



Stahl verzinkt
Steel zinc plated
Acier zingué

Stahl verzinkt
Steel zinc plated
Acier zingué



Ø 3,0 mm

D1 = 3,0 + 0,08 / - 0,1 mm

D2 = 6,5 + 0 / - 0,7 mm

k = 0,8 +/- 0,2 mm

d = 1,9 mm

P ≥ 27,0 mm

L = + 1,0 / - 0,2 mm

3,1 mm

	F-Max		CODE				
3,0 x 5,0 mm	9,4 mm	0,5 - 1,5 mm	70801 30500	915 N	1125 N	1000	10000
3,0 x 6,0 mm	10,4 mm	1,5 - 3,0 mm	70801 30600			1000	10000
3,0 x 8,0 mm	12,4 mm	3,0 - 5,0 mm	70801 30800			1000	10000
3,0 x 10,0 mm	14,4 mm	5,0 - 7,0 mm	70801 30100			1000	10000
3,0 x 12,0 mm	16,4 mm	7,0 - 9,0 mm	70801 30120			1000	10000
3,0 x 14,0 mm	18,4 mm	9,0 - 11,0 mm	70801 30140			1000	10000
3,0 x 16,0 mm	20,4 mm	11,0 - 13,0 mm	70801 30160			1000	10000
3,0 x 18,0 mm	22,4 mm	13,0 - 15,0 mm	70801 30180			1000	10000
3,0 x 20,0 mm	24,4 mm	15,0 - 17,0 mm	70801 30200			500	5000
3,0 x 25,0 mm	29,4 mm	17,0 - 22,0 mm	70801 30250			500	5000

Ø 3,2 mm

D1 = 3,2 + 0,08 / - 0,1 mm

D2 = 6,5 + 0 / - 0,7 mm

k = 0,8 +/- 0,2 mm

d = 2,0 mm

P ≥ 27,0 mm

L = + 1,0 / - 0,2 mm

3,3 mm

	F-Max		CODE				
3,2 x 5,0 mm	9,9 mm	0,5 - 1,5 mm	70801 32500	1060 N	1285 N	1000	10000
3,2 x 6,0 mm	10,9 mm	1,5 - 3,0 mm	70801 32600			1000	10000
3,2 x 8,0 mm	12,9 mm	3,0 - 5,0 mm	70801 32800			1000	10000
3,2 x 10,0 mm	14,9 mm	5,0 - 7,0 mm	70801 32100			1000	10000
3,2 x 12,0 mm	16,9 mm	7,0 - 9,0 mm	70801 32120			1000	10000
3,2 x 14,0 mm	18,9 mm	9,0 - 11,0 mm	70801 32140			1000	10000
3,2 x 16,0 mm	20,9 mm	11,0 - 13,0 mm	70801 32160			1000	10000
3,2 x 18,0 mm	22,9 mm	13,0 - 15,0 mm	70801 32180			1000	10000
3,2 x 20,0 mm	24,9 mm	15,0 - 17,0 mm	70801 32200			500	5000
3,2 x 25,0 mm	29,9 mm	17,0 - 22,0 mm	70801 32250			500	5000