

IG9800

**20 L/D Portable
Dehumidifier**

Product Description



- 20L/D Moisture Removal
- 340W Power Input
- Water tank capacity - 6 Litres
- Electronic LCD Display
- Adjustable humidistat between 30 and 80% RH
- Powerful rotary compressor
- Refrigerant - R-410a
- CFC free
- Overflow indicator - Yes
- Frost prevention - Yes
- Continuous drainage - Yes (13mm diameter hose)
- Upward outlet suitable for drying clothes
- Noise level 47-50 dB(A)
- Recommended for room size 26m² - 33m²

Product Information

Product Code	IG9800
Colour	White
Wattage	340W
Power Cord (m)	1.5
Energy Rating	N/A
Barcode	5016368018132
Approvals	GS, CE, EMC

Country of Origin	China		
Guarantee	1 Year		
Weight (kgs)	14.5		
Dimensions (mm)	H	W	D
	612	390	274
Internal Dimensions	H	W	D
	N/A		

Packaging /Shipping Information

Product Packaging	
Height (mm)	680
Width (mm)	420
Depth (mm)	305
Weight (kg)	16
Outer Packaging	
Height (mm)	680
Width (mm)	420
Depth (mm)	305
Weight (kg)	16
Carton Quantity	1

Waste Packaging (kgs)	
Paper/Card	1.218
Plastics	0.274

Container Quantities	
20ft	285
40ft	600
40HC	600

Commodity Code	
8479899790	

Additional Information

- 12 Litre extraction portable dehumidifier available (IG9812)