

Knurl cutter holder model LA/FL C601

For knurl cutting on lathes and automatic lathes



Application:

For producing knurl cutting profiles in accordance with DIN 82 RAA, RBR 15°, RBL 15°, RBR 30° and RBL 30° in steel, stainless steel, non-ferrous metals and cast iron material groups.

Execution:

- high-strength steel tool holder for one knurl cutter, with cemented carbide bushings

Advantage:

- Compact and robust holder design for high process stability for small components
- User-friendly setting without disassembly
- cemented carbide bushings minimise maintenance costs



Art. no.	19100 543
Brand	QUICK
Manufacturer Part Number	32000318
For min. workpiece diameter	1.5 mm
For max. workpiece diameter	12 mm
Suitable for knurling wheel diameter	8.9 mm
Shank width	10 mm
Shaft height	10 mm
Tool design	Left
Gross Weight	0.189 kg
Product Group	192