

Automatic welding helmets

model: 9100

 **Speedglas™**

Application:

For MIG/MAG and WIG welding, manual metal arc welding, plasma arc welding, tack welding and grinding

Execution:

- Patented comfort headband for enhanced comfort also with the mask flipped up
- Optimum results for versatile welding thanks to a choice of seven protection levels (5, 8, 9-13)
- Enhanced ear and side protection provide additional safety
- Lateral valves allow exhaled air to escape more easily
- Power supply: Lithium button cell (approx. 2800 hours operating time for ref. no. 310, approx. 2500 hours operating time for ref. no. 320 and approx. 2000 hours operating time for ref. no. 330)
- Switching time from light to dark: 0.1 ms



Art. no.	55733 330
Brand	SPEEDGLAS
Manufacturer Part Number	7000000219
Category	II
EN standard	166, 175, 379
Classification according to EN 379	1 / 1 / 1 / 2
Model	9100 XX
Width of glass	107 mm
Glass height	73 mm
Min./max. protection level	5-13
Translucency when not activated	Protection level 3
Gross Weight	3.830 kg
Product Group	5SC

EAN

4046719186839