

## Balancer with load capacity of 15.0-55.0 kg, with automatic lock

Type 7236, cable extension 2000 mm, rustproof

AUTOSTAT

### Application:

Areas of application include, e.g.: Meat packing machines, welding tongs, sawing machines, etc.

### Execution:

- Housing and the cable drum made of aluminium sand cast
- Cable drum ball-bearing
- Suspension via a freely turning and swivelling safety snap hook
- Carrying force is infinitely variable via adjusting screw
- Load is attached via a screw snap hook
- cable feed limitation is impact absorbing and adjustable
- If required, the cable can be replaced very easily
- Safety device: Fall arrester in line with DIN 15112 included in scope of delivery, spring safety device, riveted special motive spring, cable drum, can be blocked with integrated locking device
- Working area: Cable extraction: 2000 mm, ropes in special lengths available on request
- Automatic stop allows the device to be locked. Locking not to be used for load change!

### Advantage:

- Effortless work



<b>Art. no.</b>	<b>77001 686</b>
<b>Brand</b>	AUTOSTAT
<b>Manufacturer Part Number</b>	77001686
<b>Min. load-carrying capacity</b>	25 kg
<b>Max. load-carrying capacity</b>	35 kg
<b>Type</b>	7236
<b>With automatic locking</b>	Yes
<b>Max. cable pull-out length</b>	2000 mm
<b>Adjustable cord length</b>	No
<b>Material of cord</b>	Stainless Steel
<b>Wire cable diameter</b>	3 mm
<b>Replaceable cord</b>	Yes
<b>Cord in-feed restriction</b>	Absorbs impacts, adjustable
<b>Material of cable drum</b>	Gravity die-cast aluminium
<b>Suspension type</b>	Freely rotating and pivot screw karabiner hook
<b>Load attachment</b>	Screw Karabiner hook
<b>Material of housing</b>	Gravity die-cast aluminium
<b>Surface</b>	Uncoated
<b>Housing width</b>	223 mm
<b>Housing thickness</b>	150.5 mm
<b>Design</b>	All external components made of non-rusting material
<b>Height</b>	530 mm
<b>Spring design</b>	Riveted special mainspring
<b>With overrotation protection</b>	No
<b>Spring breakage protection</b>	Yes
<b>Number of springs</b>	1 PCS
<b>DIN</b>	15112
<b>Gross Weight</b>	10.000 kg
<b>Product Group</b>	7EB

### EAN

4053625360475