

CDCL STB DATASHEET



MODEL	CDCL STB SERIES			
PART NUMBER	CDCL3000C0-002R85STB			
Version	Revision of historical records			

FEATURES

Low ESR & High Power Density

Over 1,000,000 duty cycles

Threaded connection

APPLICATIONS	
EV/HEV	Heavy duty machinery
Hybrid drive trains	Locomotive engine startup system
Mass transportation braking energy recovery sys	tem




CONSTRUCTION & DIMENSIONS

1) Construction

Inside structure: fold anode and cathode electrode with separator Outer structure: aluminum case, insulating sleeve

2) Dimensions



SPECIFICATIONS						
Items	Characteristics					
Operating Voltage	2.85V DC					
Surge Voltage	3.0V DC					
Operating Temperature Range	-40°C to 65°C					
Capacitance Tolerance	0% to +20% (25°C)					
Temperature Performance (-40°C to 65°C)	$\Delta C \le 5\%$ of rated value @ 25°C $\Delta ESR \le 50\%$ of rated value					
Life (1,500 hours @ 65°C, 2.85V DC)	$\Delta C \le 20\%$ of rated value $\Delta ESR \le 100\%$ of rated value					
Cycle life (1,000,000 cycles between V _R and 1/2V _R)	$\Delta C \le 20\%$ of rated value $\Delta ESR \le 100\%$ of rated value					



DETAIL SPECIFICATIONS

CAP (F)	Part Number	ESR(mΩ)		LC	MAX.	Max.	Max.	Max.	Typical Thermal	Typical	Typical
		AC@ 1kHz Max.	DC Max.	(mA, RT 72hrs)	Energy Energy Stored Density (Wh) (Wh /kg)	Density	Continuous Current (15/40°C, A)	Peak Current (A)	Resistance (R th,°C/W)	Thermal Capacitance, (C th, J/°C)	Mass (g)
3000	CDCL3000C0- 002R85STB	0.24	0.32	14.5	3.38	6.2	123/201	2184	3.1	645	548

All rights reserved. Design and specifications are subjected to change without notice.

NINGBO CRRC NEW ENERGY TECHNOLOGY CO.,LTD.

Add: No.199 Shidai Road,Wuxiang Town,Yinzhou District, Ningbo,Zhejiang,China Email: info@spscap.com Website: www.spscap.com

Document number: DT14-07-202004 Rev. & Date: V2020-1 2020.11.12



2.85V CDCL-STB Series