

BNC Male Crimp





Specifications


Impedance : 50Ω
 Frequency Range : 0-4Ghz
 Working Voltage : 500Vrms @ sea level
 Temperature Range : -65°C to +165°C
 Insulation Resistance : 5kMΩ min.

For RG-58, 58A, 58C, 141, 141A, Belden 8240, 9907, 8259, 8262, 9201, 9310, 9311 & Comm/Scope 0268


Diagram



RECOMMENDED CRIMP DIE: .068"



RECOMMENDED CRIMP DIE: .213"



RECOMMENDED STRIPPING DIMENSIONS

Dimensions : Inches (Millimetres)

No.	Description	Material	Finish	Qty
1	Shell	Brass	Nickel, 100µ"	1
2	Body	Brass	Nickel, 100µ"	1
3	Insulator	Delrin	-	1
4	Gasket	Rubber	-	1
5	Retaining Ring	Brass	Nickel, 100µ"	1
6	Spring	SK-5	Nickel, 200µ"	1
7	Washer	Brass	Nickel, 100µ"	1
8	Pin	Brass	Gold, 3µ"	1
9	Ferrule	Brass	Nickel, 100µ"	1

Part Number Table

Description	Part Number
BNC Male Crimp Plug, N,G,D for RG58/U, CBL GRP C	MC002016

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.