




# **Z-Foil Ultra High-Precision SMT Resistor** (Molded, J-Lead Terminal)





Resistance value, in ohm, is expressed by a series of six characters, five of which represent significant digits. R or K is a dual-purpose letter that designates both the value range (R for ohmic; K for kilo-ohm) and the location of the decimal point.


\* Imprinting indicates up to 3 significant digits but ordered resistance value is traceable by date code




# **FEATURES**

- Temperature coefficient of resistance (TCR): 0.05 ppm/°C typical (0°C to +60°C) by New Generation Z-Foil Technology
- 0.2 ppm/°C typical (-55°C to +125°C, +25°C ref.)
- Resistance tolerance: to ±0.01%
- Power coefficient "ΔR due to self heating": 5 ppm at rated power (typical)
- Power rating: to 200 mW (MPP) and 250 mW (MQP) at
- Load life stability: to ±0.005% at 70°C, 2000h at rated power (typical)
- Not restricted to standard values, we can supply specific "as required" values at no extra cost or delivery (e.g., 1K2345 vs. 1K)


TCR, RESISTANCE RANGE, TOLERANCE, RATED POWER								
Туре	TCR (ppm/°C) -55°C to +125°C	Resistance Range (Ω)	Resistance Tolerance (%)	Rated Power (W) at 125°C				
	±0.2±3.8	30 to <50	±0.1(B)					
	±0.2±2.8	50 to <100	±0.1(B)	0.1				
MPP	±0.2±1.8	100 to <1k	±0.1(B) ±0.05(A) ±0.02(Q)					
		1k to <20k	±0.1(B) ±0.05(A) ±0.02(Q) ±0.01(T)					
	±0.2±3.8	30 to <50	±0.1(B)					
	±0.2±2.8	50 to <100	±0.1(B)					
MQP	±0.2±1.8	100 to <1k	±0.1(B) ±0.05(A) ±0.02(Q)	0.125				
		1k to <40k	±0.1(B) ±0.05(A) ±0.02(Q) ±0.01(T)					







PERFORMANCE							
Dorometero	Test Condition	Specification		Typical			
Parameters	lest Condition	MP/MQ	MPP/MQP	MPP/MQP			
Maximum Rated Operating Temperature Working Temperature Range Maximum Working Voltage Maximum Working Current		125°C -65°C to +175°C MP = 50V, MQ = 100V 350 mA					
Thermal Shock Overload	-65°C/30 min.↔+150°C/30 min., 5 cycles Rated Voltage x 2.5, 5 sec.	±0.05% ±0.05%	±0.01% ±0.01%	±0.005% ±0.005%			
Low Temperature Storage and Life Outstanding PC Board Bending	-65°C, No Load, 24 hrs.→Rated Voltage, 45 min. 3 mm Bend, 60 sec.	±0.05% ±0.05%	±0.01% ±0.01%	±0.005% ±0.005%			
Dielectric Withstanding Voltage Insulation Resistance	AC 200V, 1 min. DC 100V, 1 min.	±0.01% ±0.01% ±0.005% over 10,000 MΩ					
Resistance to Soldering Heat Moisture Resistance	260°C, 10 sec. +65°C to -10°C, 90% RH to 98% RH, Rated Voltage, 10 cycles (240 hrs.)	±0.05% ±0.05%	±0.03% ±0.03%	±0.01% ±0.01%			
Shock Vibration, High Frequency	100G, 6 ms, Sawtooth Wave, X, Y, Z, each 10 shocks 20G, 10 Hz to 2,000 Hz to 10 Hz, 20 min., X, Y, Z, each 2.5 hrs.		±0.02% ±0.02%	±0.01% ±0.01%			
Storage Life	15°C to 35°C, 15% RH to 75% RH, No Load, 10,000 hrs.	±0.005%	±0.005%	±0.0025%			
High Temperature Exposure	175°C, No Load, 2,000 hrs.	±0.05%	±0.05%	±0.03%			
Life	70°C, Rated Power, 1.5 hr. – on, 0.5 hr. – off, 2,000 hrs. 70°C. Rated Power × 2. 1.5 hr. – on, 0.5 hr. – off, 2,000 hrs.	_	±0.01% ±0.03%	±0.005% ±0.01%			



# PRECAUTION IN USING FACE-BONDED CHIP RESISTORS

Storage conditions or environment may adversely affect solderability of the exterior terminals. Do not store in high temperature and humidity. The recommended storage environment is lower than 40°C, has less than 70% RH humidity and is free from harmful gases such as sulphur and chlorine.

### 2. Caution in Soldering

• Hand Soldering—Hand soldering is applicable as shown at right. Recommended

350

310

<u>년</u> 270

Applicable

Not Applicable

20 30 40 50 60 (sec

- Temp. of iron tip: 240°C to 270°C
- Power of iron: 20W or less · Diameter of tip: dia. 3 mm max.
- Solder Reflow in Furnace Recommended
  - Peak temperature: 250+0/-5°C
  - Holding time: 10 sec. max.
  - To cool gradually at room temperature
- Opping in Solder (Wave or Still) Recommended
  - Temp. of solder: 260°C max
  - Length of dipping: 10 seconds
  - · To cool gradually at room temperature


Corrosion-free flux, such as rosin, is recommended. Do not apply pressure to the molded housing immediately after soldering.

#### 3. Cleaning

Use volatile cleaner such as methylalcohol or propyl alcohol.

### 4. Circuit Board Design

The dimensions of solder land must be determined in conformity with the size of resistors and with the soldering method. They are also subject to the mounting machine and the material of the substrate. See example below.



Type	А	В	С	D
MPP	1.6 to 2.0	0.5 to 1.5	2.2 to 2.6	1.8
MQP				2.5

When parts are mounted on a board in high density, solder can possibly attach to the resistors in an excessive amount to affect performance or reliability of the resistors. To prevent this effect, the use of solder resist is recommended to isolate solder lands.