

Platform scales EOC



Application:

for versatile use in various locations such as production, warehousing and shipping.

Execution:

- Quantities, percentage determination, totalling function
- Display unit (degree of protection IP65) with 1.5 m cable
- Options: Stand for display unit
- Practical flip/flop evaluation device: various position options e.g. free-standing or screwed to the wall (optional).
- Backlit LCD display with 24 mm digit size

Delivery:

with mains adapter



Art. no.	44607 107
Brand	KERN
Manufacturer Part Number	EOC 100K-2L
Type description	EOC 100K-2L
Max. weight measuring range	60 kg
Max. weight measuring range 2	150 kg
Digit increment, weight	20 g
Digit increment 2, weight	50 g
Plate size	400 x 500 mm
With unit counting	Yes
Min. item weight	50
Data transmission type	RS232
Gross Weight	13.000 kg
Product Group	447

EAN

4045761192225