

Cordless drill driver XGT

DF001GZ



Execution:

- Cordless drill driver with 2-speed transmission for high speed
- Selector switch for easy adjustment of the assembly torque, visual confirmation of the selected torque on the digital display
- Deep discharge protection. The machine switches off automatically when the battery is almost empty.
- Active Feedback Sensing Technology (AFT) stops the motor when the tool is blocked



Art. no.	71029 507
Model	DF001GZ
Number of rechargeable batteries/batteries	0
Battery included	No
Motor design	Brushless motor
Battery voltage	40 V/AC
Applications	Heavy screw/drill application
Manufacturer Article Number	DF001GZ
Max. drilling diameter in steel	20 mm
Max. drilling diameter in wood	76 mm
Idle speed 1st gear min.	0 rpm
Idle speed 1st gear max.	650 rpm
Idle speed 1st gear min./max.	0-650 rpm
Idle speed 2nd gear min.	0 rpm
Idle speed 2nd gear max.	2600 rpm
Idle speed 2nd gear min./max.	0-2600 rpm
Max. idle speed	2600 rpm
Min. idle speed	0 rpm
Min./max. idle speed	0-2600 rpm
Max. torque for soft screwing application	68 Nm
Max. torque for hard screwing application	140 Nm
Max. torque hard/soft	140 / 68 Nm
Torque levels	41
Length	181 mm
Width	86 mm
Height	282 mm
Length x width x height	181 x 86 x 282 mm
Min./max. drill chuck span width	1.5-13 mm
Max. drill chuck span width	13 mm
Min. drill chuck span width	1.5 mm
Product Group	Prod. Gr. 715

EAN

0088381892179