

Flat spiral lathe chuck DURO-M DIN 6350, shape A

Hand chuck, for rear screw fittings



Application:

The Duro-M is a manually operated rotary lathe chuck with spiral ring and through hole. It is mainly used on conventional lathes for machining turned parts.

Execution:

- Chuck body (and all other components) made of steel
- Centric clamping
- High clamping force
- High concentricity
- Optimised for weight and mass inertia
- Minimum interference contour
- Three-jaw lathe chuck
- The Duro-M is also available with double jaw guide as an option.

Advantage:

- Workpieces with different clamping diameters can be clamped very quickly and without repositioning the jaws.
- Control edge
- Use on conventionally clamping, horizontal and vertical lathes as well as milling machines, rotary tables and dividers.

Delivery:

Ref. no. 22386011-22386072 Scroll lathe chuck 3-jaws with drilling and turning jaws

Ref. no. 22411021-22411081 Scroll lathe chuck 3-jaws with plain jaws and reverse top jaws.

The matching chuck key is included in the scope of delivery.



Art. no.	22411 031
Brand	RÖHM
Manufacturer Part Number	185311
Outer diameter	125
Number of jaws	3 PCS
DIN	6350-1
Clearance hole	32 mm
Pitch circle diameter	108
Centring diameter	95
Square width	9
Depth	4
Length 2	56 mm
Height	61 mm
Length	20 mm
Max. rotation speed	5500
Tension force	31
Max. torque	80 Nm
Weight	4.988 kg
Gross Weight	4.988 kg
Product Group	203

EAN

4019208526911