

Assembly trolley with CLIP-O-FLEX hook-on system

With pull-out system and CLIP-O-FLEX trays

CLIP-O-FLEX®

Application:

Thanks to the flexible and modular CLIP-O-FLEX system, the assembly trolley can be optimally designed and adapted to the individual work sequences in production, assembly, development, training and further education. CLIP-O-FLEX sets your work/storage area or your organisation system with one clip and at the same time gives the highest level of horizontal and vertical flexibility.

Version:

- Solidly welded sheet steel structure with painted multiplex panel, 30 mm stark
- Workbench panel with CLIP-O-FLEX support rails installed on the top of the housing left, right and at the rear
- With convenient pull-out system incl. CLIP-O-FLEX trays with hook-in angles 0/40/80°
- Running gear with 2 fixed wheels and 2 steering rollers, including 1 steering roller with stopper
- Central locking with cylinder lock incl. 2 keys

Advantage:

- Simply remove the trays from the cabinet and hang on the hook-in rails at the side
- Flexible hook-on system with only one hooking movement
- Ergonomic workplace design thanks to different inclines and can be relocated horizontally
- Quick access to work equipment, very clear overview
- Rapid conversion and replacement, highest possible level of mobility, less walking required, optimum use of space



Art. no.	50237 135
Height	958 mm
Width	474 mm
Depth	405 mm
Central locking	Yes
Lock type	Cylinder lock
With sliding handle	Yes
Load-carrying capacity	550 kg
Dynamic load-carrying capacity	225 kg
Number of fixed rollers	2 PCS
Number of steering rollers	2 PCS
Material of wheel	Solid rubber
Wheel diameter	100 mm
Material	Sheet steel
Body colour	Optional
Colour of front	Optional
Surface	Powder-coated