




AMP

TE Internal #: 380306-3

Insertion & Extraction Tools, Contact Insertion, Contact-to-Printed Circuit Board

[View on TE.com >](#)

Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Insertion**

Insertion & Extraction Tool Application: **Contact-to-Printed Circuit Board**

**Features**

**Product Type Features**

Insertion & Extraction Tool Type	Contact Insertion
Insertion & Extraction Tool Application	Contact-to-Printed Circuit Board

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An

Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts




TE Part # 42574-3  
PIDG, TAPER PIN




TE Part # 41650  
TAPER PIN, ON STRIP, TIN-L; 53SER




TE Part # 41652  
TAPER PIN, ON STRIP, GOLD; 53SER




TE Part # 42575-3  
PIDG, TAPER PIN




TE Part # 42575  
PIDG, TAPER PIN



TE Part # 42575-1  
PIDG, TAPER PIN



TE Part # 42634-3  
PIDG, TAPER PIN



TE Part # 42637-3  
PIDG, TAPER PIN

## Customers Also Bought



TE Part #2825213-1  
VAL-U-LOK SKT HCS SN 22-18 LP



TE Part #5-2176405-6  
3550 10M 5%



TE Part #1-2329389-1  
PB OFF/ON FC YLW M1 TERM WHI  
LED IP68 50



TE Part #YDTS26F13-04SEV001  
Straight Plug: D38999, 13-04 Insert,  
Electroless Nickel Plating



TE Part #2170773-1  
CAGE ASSY, QSFP28 1X1, SPRING, LP



TE Part #2-456406-5  
WIRE CRIMPER .090



TE Part #2-1609998-3  
KEV 42A 2S SP WYE BS 440VAC



TE Part #2176429-5  
MPT100 R47 5%



TE Part #3750940003  
S02-07-R-3CS925



TE Part #2-1618108-3  
WOV-3-440=WILMAR OVERVOLTAGE  
4

## Documents

### Product Drawings

[CLIT FOR 53 SERIES TP](#)

English

---

### Datasheets & Catalog Pages

[Insertion-Extraction-Tool-2345721-1](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

---

### Instruction Sheets

[CERTI-LOK Taper Pin Insertion Tool](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[Adjustment & Repair of CERTI-LOK Taper Pin Insertion Tools](#)

English