

## HNS 55 W G13

PURITEC HNS Germicidal Lamps | Germicidal ultraviolet lamps

### Areas of application

- Efficient disinfecting of air, water and surfaces



### Product benefits

- Effective and environment-friendly disinfection without chemicals
- Low mercury content
- Long lifetime due to specific coating
- Ozone-free

### Product features

- Dominant wavelength: 254 nm (OFR version)



# Product datasheet

## Technical data

### Electrical data

Nominal voltage	83.0 V
Construction voltage	83.00 V
Nominal current	0.77 A
Lamp current	0.77 A
Nominal wattage	55.00 W

### Photometrical data

Radiated power 200...280 nm (UVC)	18.0 W
-----------------------------------	--------

### Dimensions & weight



Diameter	26.0 mm
Length	895.0 mm

### Lifespan

Lifespan	9000 h
----------	--------

### Additional product data

Base (standard designation)	G13
-----------------------------	-----

### Capabilities

Dimmable	No
Burning position	Any

### Country specific categorizations

Order reference	HNS 55W G13
-----------------	-------------

## Product datasheet

---

### Safety advice

PURITEC germicidal lamps emit high-intensity UV radiation that can cause sunburn and conjunctivitis. The skin and eyes must therefore not be exposed to direct or reflected unfiltered radiation.

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899083936	HNS 55 W G13	Sleeves 1	907 mm x 32 mm x 29 mm	0.84 dm <sup>3</sup>	142.00 g
4052899103375	HNS 55 W G13	Shipping carton box 25	930 mm x 150 mm x 155 mm	21.62 dm <sup>3</sup>	4414.00 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

---