

ITEM	PART#	DESCRIPTION	QTY	UOM
A	5055700401	2.0W/B SINGLE REC HSG 4CKT BLK	1	PC
B	5055721000	2.0W/B REC CRIMP TERM CHAIN H>F	4	PC
C	--	PAPER PRINTED PAPER WHITE	1	PC

FROM	TO	DESCRIPTION	COLOR
A1	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A2	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A3	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A4	--	1X22AWG DISC SR-PVC BK UL10002	BLACK




TABLE			
PART NUMBER	L1	L2(REF)	TITLE
2181021040	50±3	12	MICROLOCK PLUS 2.0 RS 4CKT 50MM DISC Sn
2181021041	100±5	37	MICROLOCK PLUS 2.0 RS 4CKT 100MM DISC Sn
2181021042	150±8	62	MICROLOCK PLUS 2.0 RS 4CKT 150MM DISC Sn
2181021043	300±10	137	MICROLOCK PLUS 2.0 RS 4CKT 300MM DISC Sn
2181021044	600±10	287	MICROLOCK PLUS 2.0 RS 4CKT 600MM DISC Sn

MOLEX P/N
MOLEX
BATCH WK/YR
DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2021/03/12	A	INITIAL RELEASE	AS20

- NOTES**
- CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
 - FREE ENDS MUST BE STRIPPED, TWISTED & TINNED. THE LENGTH OF TINNING IS 5±1MM. TINNING DIA MUST BE 0.9MM MAX.
 - LABEL TEXT MUST BE 2MM MAX IN HEIGHT WITH ARIAL FONT.
 - LABEL MUST BE WRAPPED IN FLAG TYPE.

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex
	DIMENSION UNITS	SCALE	EC NO: 665161 DRWN: AS20 CHK'D: RDESAI01 APPR: RDESAI01		
DIVISIONAL SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		2021/03/12		SEE TABLE
	ANGULAR TOL ± °		2021/05/26		
4 PLACES ±		2021/05/26		PRODUCT CUSTOMER DRAWING	
3 PLACES ±		INITIAL REVISION:		DOCUMENT NUMBER	
2 PLACES ±		DRWN: AS20		2181021040	
1 PLACE ±		APPR: RDESAI01		DOC TYPE	
0 PLACES ±		2021/03/12		PSD	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DOC PART	
		DRAWING		000	
		SERIES		REVISION	
		A4-SIZE		A	
		218102		MATERIAL NUMBER	
				SEE TABLE	
				CUSTOMER	
				GENERAL MARKET	
				SHEET NUMBER	
				1 OF 1	