

BLINDNIETE



FLACHRUNDKOPF (~ DIN EN ISO 15981)

BLIND RIVETS

DOMED HEAD (~ DIN EN ISO 15981)

RIVETS AVEUGLES


TÊTE PLATE (~ DIN EN ISO 15981)









Aluminium AIMG 2,5
Aluminium AIMG 2,5
Aluminium AIMG 2,5


Aluminium Legierung
Aluminium alloy
Aluminium alliage







Ø 3,0 mm

D1 = 3,0 + 0,08 / - 0,1 mm
D2 = 6,5 + 0 / - 0,7 mm
k = 0,8 + / - 0,2 mm
d = 1,95 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 3,1 mm


	F-Max		CODE				
3,0 x 4,0 mm	8,4 mm	0,5 - 1,5 mm	70705 30400	400 N	550 N	1000	10000
3,0 x 6,0 mm	10,4 mm	1,5 - 3,0 mm	70705 30600			1000	10000
3,0 x 8,0 mm	12,4 mm	3,0 - 5,0 mm	70705 30800			1000	10000
3,0 x 10,0 mm	14,4 mm	5,0 - 7,0 mm	70705 30100			1000	10000
3,0 x 12,0 mm	16,4 mm	7,0 - 9,0 mm	70705 30120			1000	10000







Ø 3,2 mm

D1 = 3,2 + 0,08 / - 0,1 mm
D2 = 6,5 + 0 / - 0,7 mm
k = 0,8 + / - 0,2 mm
d = 1,95 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 3,3 mm

	F-Max		CODE				
3,2 x 6,0 mm	10,9 mm	1,5 - 3,5 mm	70705 32600	535 N	670 N	1000	10000
3,2 x 8,0 mm	12,9 mm	3,5 - 5,0 mm	70705 32800			1000	10000
3,2 x 10,0 mm	14,9 mm	5,0 - 7,0 mm	70705 32100			1000	10000
3,2 x 12,0 mm	16,9 mm	7,0 - 8,5 mm	70705 32120			1000	10000
3,2 x 14,0 mm	18,9 mm	8,5 - 10,5 mm	70705 32140			1000	10000
3,2 x 16,0 mm	20,9 mm	10,5 - 13,0 mm	70705 32160			1000	10000

Ø 4,0 mm

D1 = 4,0 + 0,08 / - 0,15 mm
D2 = 8,0 + 0 / - 1,0 mm
k = 1,0 + / - 0,3 mm
d = 2,45 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 4,1 mm

	F-Max		CODE				
4,0 x 6,0 mm	10,9 mm	1,5 - 3,5 mm	70705 40600	845 N	1025 N	1000	10000
4,0 x 8,0 mm	12,9 mm	3,5 - 5,0 mm	70705 40800			1000	10000
4,0 x 10,0 mm	14,9 mm	5,0 - 6,5 mm	70705 40100			1000	10000
4,0 x 12,0 mm	16,9 mm	6,5 - 8,5 mm	70705 40120			1000	10000
4,0 x 14,0 mm	18,9 mm	8,5 - 10,5 mm	70705 40140			500	5000
4,0 x 16,0 mm	20,9 mm	10,5 - 12,5 mm	70705 40160			500	5000
4,0 x 18,0 mm	22,9 mm	12,5 - 14,5 mm	70705 40180			500	5000
4,0 x 20,0 mm	24,9 mm	14,5 - 16,5 mm	70705 40200			500	5000