




**LED element**

**Part no.** M22-FLED-RGB  
**Article no.** 180800  
**Catalog No.** M22-FLED-RGB

**Delivery program**

Product range			Accessories
Single unit/Complete unit			Single unit
Description			Cage Clamp is a registered trademark of Wago Kontakttechnik GmbH/Minden, Germany
Fixing			Front fixing
Connection technique			Cage Clamp
Rated operational voltage	$U_e$	V	24 V DC
<b>Rated operational current</b>	$I_e$	mA	8 - 15
Power consumption	$P_{max.}$	W	0.36
			at 24 V
<b>Colour</b>			
			red/green/blue
Degree of Protection			IP20
Connection to SmartWire-DT			no

**Notes**

For indicator lights, illuminated pushbutton actuators, and illuminated selector switch actuators, the following applies: Only in combination with M22-...-W

Terminal diagram:

	Colors	Pin	X1	X2	X3	X4
		X1 +R		+G	+B	GND
M22-FLED-RG	red	x				x
	green		x			x
	yellow	x	x			x
M22-FLED-RGB	red	x				x
	green		x			x
	yellow	x	x			x
	White	x	x		x	x
	blue				x	x
	Violet	x			x	x
	Turquoise		x		x	x

**Technical data**

**General**

Standards			IEC 60947-5-1
Climatic proofing			Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30 Dry heat to IEC 60068-2-2
Ambient temperature			
Open		°C	-25 - +70
Storage		°C	- 40 - + 85

Mounting position			As required
Terminal capacities		mm <sup>2</sup>	
Solid		mm <sup>2</sup>	1 x 1 (0.2 - 1.5) 1 x 1 (075 - 1.5) Can be plugged without tools
Stranded		mm <sup>2</sup>	1 x 1 (0.2 - 1.5)
Flexible with ferrule		mm <sup>2</sup>	1 x 1 (0.25 - 1) Use WAGO Variocrimp 4 crimping tool; please enquire for others
Solid or stranded		AWG	1 x 1 (24 - 16)

### Contacts

Rated impulse withstand voltage	U <sub>imp</sub>	V AC	4000
Rated insulation voltage	U <sub>i</sub>	V	250
Overvoltage category/pollution degree			III/3
Indoor and protected outdoor installation			

### Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	70

### Technical data ETIM 6.0

Low-voltage industrial components (EG000017) / Lamp holder block for control circuit devices (EC000204)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Bulb socket block for command and alarm devices (ec1@ss8.1-27-37-12-09 [AKF027011])			
With integrated transformer			No
With integrated voltage decreasing resistor			No
With integrated lamp			Yes
With integrated diode			Yes
Lamp holder			None
Rated voltage U <sub>e</sub> at AC 50 Hz		V	0 - 0
Rated voltage U <sub>e</sub> at AC 60 Hz		V	0 - 0
Rated voltage U <sub>e</sub> at DC		V	24 - 24
Voltage type for actuating			DC
Type of lamp			LED
Connection type auxiliary circuit			Spring clamp connection
Colour lamp			-
Type of fastening			Front fastening

## Dimensions

