
# **Resistors**

# **Electronics**

# **Radial Ceramic Case Resistors** Wirewound / Metal Oxide

#### **SQM / CVF / CVW Series**

- 2 to 10 watts
- Resistance OR1 to 200K
- High overload capability
- Flameproof case
- Small PCB footprint
- **RoHS** compliant




All parts are Pb-free and comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)

## **Electrical Data**

		SQM2 / CV-2	SQM3 / CV-3	SQM5 / CV-5	SQM7 / CV-7	SQM10 / CV-10	SQM10A / CV-10
Power rating at 70°C	watts	2	3	5	7	10	10
Resistance range – wirewound (C)	VW) ohms	0R1 - 27R	0R1 - 39R	0R1 - 47R	0R1 - 680R	0R1 - 910R	0R1 - 560R
Resistance range – oxide (CVF)	ohms	30R – 33K	43R – 56K	51R – 100K	750R - 200K	1K0 - 200K	
Limiting element voltage vol	lts dc or ac rms	150	300	350	500	750	750
Thermal impedance	°C/watt	50	45	30	28	23	23
Isolation voltage	1000						
TCR	ppm/°C	<20R: ± 400, ≥20R: ± 350					
Resistance Tolerance	%	± 5 ± 10					
Standard Values		E24					
Ambient temperature range	bient temperature range °C -55 to +155°C						

# Physical Data (all dimensions in mm, weights in g)

Туре	<b>L</b> ± 1.0	<b>W</b> ± 1.0	<b>D</b> ± 1.0	<b>B</b> ± 1.0	<b>E</b> ± 1.0	<b>F</b> ± 1.0	<b>P</b> ± 1.0	<b>d</b> ±0.05	Weight Nom.
SQM2/CV-2	20	11.5	7.5	4.5	3.0	3.0	5	0.7	4.3
SQM3 / CV-3	25	12.5	8.5	4.5	4.0	4.0	5	0.7	5.6
SQM5 / CV-5	25	12.5	9	5.0	3.5	3.5	5	0.8	6.3
SQM7 / CV-7	38	12.5	9	5.0	2.75	5.0	5	0.8	10.7
SQM10/ CV-10	50	12.5	9	4.25	2.75	5.0	5	0.8	13.4
SQM10A / CV-10	35	16.0	12	6.0	4.25	4.25	7.5	0.8	13.8



#### Construction

A high purity ceramic rod, with force fit end caps onto which is wound a wire element: or a desposited metal oxide film (depending on value). The element is fitted into a ceramic case with fireproof insulation cement.

# **Radial Ceramic Case Resistors** Wirewound / Metal Oxide

#### **SQM / CVF / CVW Series**



#### **Termination Details:**

Material The 100% Sn finish copper lead wires are internally welded to the resistance element end caps.

The terminations meet the requirements of IEC 115-1 Clause 4.17.3.2 Solderability

The terminations meet the requirements of IEC 86.2.21 Strength

**Marking:** Type reference, resistance value and tolerance are legend marked onto the upper surface.

Flammability: The resistor will not burn under any condition of applied temperature or overload.


Solvent resistance: The body protection and marking are resistant to all normal industrial solvents suitable for printed

circuits.

### **Performance Data**

		Maximum		
Load at rated power (1000hrs at 70°C)	ΔR	<100K: 5% ≥100K: 10%		
Derating from rated power at 70°C	power at 70°C See Graph			
short term overload (lesser of 6.25 x Pr or 2.5 x LEV for 5s)	ΔR	5% +0.05Ώ		
Damp heat steady state (56 days, 40°C, ≥90% RH)	ΔR	5% +0.05Ω		
Temperature rapid change (5 cycles -55°C to +155°C)	ΔR	2% +0.05Ω		
Resistance to solder heat	ΔR	1% +0.05Ώ		
Voltage Proof (1kV for 60s)		No evidence of flashover, mechanical damage, arcing or insulation breakdown		
Solderability		Min. 95% coverage		

#### **Temperature Derating**




SQM / CVF / CVW Series



# **Ordering Procedure**

This product has two valid part numbers:

European (Welwyn) Part Number: SQM3-1K2JB3 (SQM3, 1.2 kilohms ±5%, Pb-free)



1	2	3	4			
Type	Value	Tolerance	Packing & Termination Finish			
SQM2, SQM3,	E24 = 3/4 characters R = ohms K = kilohms	J = ±5%	Pb-free only			
SQM5, SQM7		K = ±10%	В3	SQM2, SQM3	3000/box	
SQM10,			B2	SQM5	2000/box	
SQM10A			B1	SQM7, SQM10	1000/box	
			B09	SQM10A	900/box	

USA (IRC) Part Number: CVF31201JLF (CVF3, 1.2 kilohms ±5%, Pb-free)



1 Type	2 Size	3 Value	4 Tolerance	5 Termination Finish	Pa	ncking
	2	3 digits + multiplier	J = ±5%	LF = Pb-free	2, 3	3000/box
CVF, CVW	3	R = ohms for values <100 ohms	K = ±10%		5	2000/box
	5				7, 10	1000/box
	7		•			
	10					