

Hinged swivel arms for workbench mounting

Double-hinged

Application:

For hooking into support struts to accommodate various modular components.

Execution:

- Made from stable rectangular steel profile 50 x 30 x 2 mm
- Slewing radius 180 °
- Maximum load capacity 25 kg



Art. no.	50239 266
Brand	HK
Manufacturer Part Number	50239266
Type	Hinged swivel arms (double-hinged) for workbench assembly
Material	Sheet steel
Gross Weight	4.000 kg
Product Group	504

EAN

4053625090501