Regulation EC No 1907/2006 Art.31

Productname :	AMBERKLENE ME20
Ref.Nr.:	UDS000347_3_20200630 (EN)

Creationdate : Replaces: 30.06.20 Version : 3.0 UDS000347_20170629

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

AMBERKLENE ME20

Bulk

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Heavy duty

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd. Wylds Road Castlefield Industrial Estate TA6 4DD Bridgwater Somerset United Kingdom Tel.: +44 1278 727200 Fax.: +44 1278 425644 E-mail : hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical:	Flammable liquid, category 3	
-	Flammable liquid and vapour.	
Classification is based or	n test data.	
Health:	Aspiration Hazard Category 1	
	May be fatal if swallowed and enters airways.	
	Specific target organ toxicity - single exposure, category 3	
	May cause respiratory irritation.	
	Specific target organ toxicity - single exposure, category 3 May cause drowsiness or dizziness.	
Classification based on c	alculation method.	
Environment:	Hazardous to the aquatic environment, chronic category 2 Toxic to aquatic life with long lasting effects.	
Classification based on c	alculation method.	
Other hazards :	Repeated exposure may cause skin dryness or cracking.	



Safety Data Sheet		Regulation EC No 1907/2006 Art.31			
Productname : Ref.Nr.:	AMBERKLENE UDS000347_3_	ME20 _20200630 (EN)	Creationdate : Replaces:	30.06.20 Version : 3.0 UDS000347_20170629	
Other haz	ards :	Not classified	Ŀ		

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier:	Contains: Hydrocarbons, C9, aromatics Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, < 2% aromatics
Hazard pictogram(s):	
Signal word:	Danger
Hazard statement(s):	 H226 : Flammable liquid and vapour. H304 : May be fatal if swallowed and enters airways. H335 : May cause respiratory irritation. H336 : May cause drowsiness or dizziness. H411 : Toxic to aquatic life with long lasting effects.
Precautionary statement(s):	 P101 : If medical advice is needed, have product container or label at hand. P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P261 : Avoid breathing dust/fume/gas/mist/vapours/spray. P271 : Use only outdoors or in a well-ventilated area. P301/310 : IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.
	P331 : Do NOT induce vomiting.
	P405 : Store locked up.
	P501-2 : Dispose of contents/container to an authorised waste collection point.
Supplemental Hazard information:	Repeated exposure may cause skin dryness or cracking.

2.3. Other hazards

No information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS- nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons, C9, aromatics	01- 2119455851- 35	-	(918- 668-5)		Flam. Liq. 3, STOT SE 3, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H226,H335,H336,H304,H411	Q



Productname :	AMBERKLENE ME20	Creationdate :	30.06.20 Version : 3.0
Ref.Nr.:	UDS000347 3 20200630 (EN)	Replaces:	UDS000347 20170629
	00000047_0_20200000 (EN)	Replaces:	000000000000000000000000000000000000000

(2-methoxymethylethoxy)propanol	01- 2119450011- 60	34590- 94-8	252- 104-2	10- 30	-	-	A
Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, < 2% aromatics	01- 2119463258- 33	-	(919- 857-5)	10- 20	Flam. Liq. 3, Asp. Tox. 1, STOT SE 3	H226,H304,H336	B,Q
Explanation notes							
A : substance with Community workplace	e exposure limit						
B : substance with national established workplace exposure limit							
Q : The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.							

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with water for at least 15 minutes Seek medical attention if irritation persists
Contact with skin :	Remove contaminated clothing immediately and wipe affected skin with dry cloth. Then wash with soap and water Seek medical attention if irritation persists
Inhalation :	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
Ingestion :	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Irritating to respiratory system. Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	Irritating to skin Symptoms : redness and pain
Eye contact :	Mildly irritating to eyes Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible
	If symptoms persist always call a doctor

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent



3 / 9

Regulation EC No 1907/2006 Art.31

Productname :	AMBERKLENE ME20	Creationdate :	30.06.20 Version : 3.0
Ref.Nr.:	UDS000347_3_20200630 (EN)	Replaces:	UDS000347_20170629

5.2. Special hazards arising from the substance or mixture

May form explosive vapour/air mixtures Forms hazardous decomposition products CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources Ensure adequate ventilation Wear suitable protective clothing including eye/face protection.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material Place in appropriate container This material and/or its container must be disposed of as hazardous waste.

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition Take precautionary measures against static discharges Equipment should be earthed Use explosion-proof electrical/ventilating/lighting/.../equipment. Use only non-sparking tools. Do not breathe aerosols or vapours. Ensure adequate ventilation Avoid contact with skin and eyes. Wash thoroughly after use Wear protective gloves/protective clothing/eye protection/face protection.



4/9

Safety Data Sheet		Regulation EC No 1907/2006 Art.31		
Productname :	AMBERKLENE ME20	Creationdate :	30.06.20 Version : 3.0	
Ref.Nr.:	UDS000347_3_20200630 (EN)	Replaces:	UDS000347_20170629	

7.2. Conditions for safe storage, including any incompatibilities

Keep container tightly closed, in a cool, well ventilated place. Keep out of reach of children.

7.3. Specific end use(s)

Cleaners - Heavy duty

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
National established exposure limits, United Kingdom			
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
National established exposure limits, Ireland			
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
		STEL	-

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation
-	Keep away from heat and sources of ignition
	Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product.
	Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equiped with organic gas/vapor cartridge (type A)
hands and skin :	When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	Nitrile
eyes :	Wear safety eyewear according to EN 166.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance : physical state :Liquid.colour :Colorless.



Regulation EC No 1907/2006 Art.31

Productname :	AMBERKLENE ME20	Creationdate :	30.06.20 Version : 3.0
Ref.Nr.:	UDS000347_3_20200630 (EN)	Replaces:	UDS000347_20170629
		•	

odour :	Characteristic odor.
рН :	Not applicable.
Boiling point/range :	140 °C
Flash point :	41 °C (Closed Cup)
Explosion limits : upper limit :	7.0 %
lower limit :	0.7 %
Relative density :	0.87 g/cm3 (@ 20°C).
Solubility in water :	Insoluble in water
Auto-ignition :	> 200 °C
Viscosity :	Not available.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity:	based on available data the classification criteria are not met
skin corrosion/irritation:	based on available data the classification criteria are not met
serious eye damage/irritation:	based on available data the classification criteria are not met
respiratory or skin sensitisation:	based on available data the classification criteria are not met



6 / 9 CRC Industries UK Limited Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,

Somerset, TA6 4DD Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Safety Data Sheet		Regulation EC No 1907/2006 Art.31		
Productname :	AMBERKLENE ME20	Creationdate :	30.06.20 Version : 3.0	
Ref.Nr.:	UDS000347_3_20200630 (EN)	Replaces:	UDS000347_20170629	

germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	based on available data the classification criteria are not met

carcinogenicity:	based on available data the classification chiena are not met
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	May cause respiratory irritation.
	May cause drowsiness or dizziness.
STOT repeated exposure:	based on available data the classification criteria are not met
aspiration hazard:	May be fatal if swallowed and enters airways.

Information on likely routes of exposure:

Inhalation :	Irritating to respiratory system. Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact :	Irritating to skin
Eye contact :	May cause irritation.

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
(2-methoxymethylethoxy)propanol	34590-94-8	LD50 oral rat	> 5000 mg/kg
		LD50 derm.rabit	> 10000 mg/kg
Hydrocarbons, C9, aromatics	-	LD50 oral rat	3492 mg/kg
		LC50 inhal.rat	> 6.393 mg/l
		LD50 derm.rabit	> 3160 mg/kg
Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, < 2% aromatics	-	LD50 oral rat	>5000 mg/kg
		LC50 inhal.rat	4951 mg/m3
		LD50 derm.rabit	>5000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, chronic category 2 Toxic to aquatic life with long lasting effects.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
(2-methoxymethylethoxy)propanol	34590-94-8	IC50 algae	> 100 mg/l
		LC50 fish	> 10000 mg/l
		EC50 daphnia	> 100 mg/l

12.2. Persistence and degradability

No information available



Safety Data Sheet		Regulation EC No 1907/2006 Art.31		
Productname :	AMBERKLENE ME20	Creationdate :	30.06.20 Version : 3.0	
Ref.Nr.:	UDS000347_3_20200630 (EN)	Replaces:	UDS000347_20170629	

12.3. Bioaccumulative potential

No information available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Do not discharge into drains or the environment, dispose to an authorised waste collection point.

SECTION 14: Transport information

14.1. UN number

UN-number : 1993

14.2. UN proper shipping name

FLAMMABLE LIQUID, N.O.S. (turpentine substitute) Proper shipping name:

14.3. Transport hazard class(es)

3 Class: F1 ADR/RID - Classification code:

14.4. Packing group

Packing group: Ш

14.5. Environmental hazards

ADR/RID - Environmentally Yes hazardous: IMDG - Marine pollutant: Marine pollutant



8/9 **CRC Industries UK Limited**

Safety Data Sheet		Regulation EC No 1907/2006 Art.31		
Productname :	AMBERKLENE ME20	Creationdate :	30.06.20 Version : 3.0	
Ref.Nr.:	UDS000347 3 20200630 (EN)	Replaces:	UDS000347 20170629	

IATA/ICAO - Environmentally hazardous:

14.6. Special precautions for user

ADR/RID - Tunnelcode:	(D/E)
IMDG - Ems:	F-E, S-E
IATA/ICAO - PAX:	355
IATA/ICAO - CAO	366

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements. Regulation (EC) No 1907/2006 (REACH) Regulation (EC) No 1272/2008 (CLP)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: -:-

H226 : Flammable liquid and vapour.
H304 : May be fatal if swallowed and enters airways.
H335 : May cause respiratory irritation.
H336 : May cause drowsiness or dizziness.
H411 : Toxic to aquatic life with long lasting effects.
Classification according to Regulation (EC) No 1272/2008 Labelling according to Regulation (EC) No 1272/2008
TWA = time weight average
STEL = short time exposure limit
VOC = volatile organic compounds
PBT = persistant bioaccumulative toxic
vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

