

ECLULTRA - LumiPRO - Luminol-Enhancer Solution

Safety data sheet

SECTION 1. Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Code: **ECLULTRA**
Product name: **LumiPRO - Luminol-Enhancer Solution**

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use: **Luminol-Enhancer Solution**

1.3. Details of the supplier of the safety data sheet

Name: **Clever Scientific Ltd.**
Full address: **Unit 41, Somers road Industrial Estate**
District and Country: **CV22 7DH Rugby**
UK
Tel. **+44(0)1788565300**

e-mail address of the competent person

responsible for the Safety Data Sheet: **info@cleaverscientific.com**

1.4. Emergency telephone number

For urgent inquiries refer to: **+44(0)1788565300 (not 24 hours) - Contact your local A&E if required**

SECTION 2. Hazards identification

2.1. Classification of the substance or mixture

The product is not classified as hazardous pursuant to the provisions set forth in EC Regulation 1272/2008 (CLP). However, since the product contains hazardous substances in concentrations such as to be declared in section no. 3, it requires a safety data sheet with appropriate information, compliant to EC Regulation 1907/2006 and subsequent amendments.

Hazard classification and indication:

2.2. Label elements

Hazard labelling pursuant to EC Regulation 1272/2008 (CLP) and subsequent amendments and supplements.

Hazard pictograms: --

Signal words: --

Hazard statements:

EUH210 Safety data sheet available on request.
EUH208 Contains:
Sodium3-(10H-phenothiazin-10-yl)propane-1-sulfonate

May produce an allergic reaction.

Precautionary statements:

ECLULTRA - LumiPRO - Luminol-Enhancer Solution

--

2.3. Other hazards

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

SECTION 3. Composition/information on ingredients**3.1. Substances**

Information not relevant

3.2. Mixtures

Contains:

The full wording of hazard (H) phrases is given in section 16 of the sheet.

Identification**Classification 1272/2008 (CLP)****TRIS**

CAS 77-86-1

 $3,5 \leq x < 4$

Eye Irrit. 2 H319, Skin Irrit. 2 H315

EC 201-064-4

INDEX -

ETHANEDIOL

CAS 107-21-1

 $1 \leq x < 1,5$

Acute Tox. 4 H302, STOT RE 2 H373

EC 203-473-3

INDEX 603-027-00-1

SODIUM 3-(10H-PHENOTHIAZIN-10-YL)PROPANE-1-SULFONATE

CAS 101199-38-6

 $0,2 \leq x < 0,25$

Eye Irrit. 2 H319, Skin Sens. 1 H317, EUH208

EC

INDEX -

SECTION 4. First aid measures**4.1. Description of first aid measures**

EYES: Remove contact lenses, if present. Wash immediately with plenty of water for at least 15 minutes, opening the eyelids fully. If problem persists, seek medical advice.

SKIN: Remove contaminated clothing. Wash immediately with plenty of water. If irritation persists, get medical advice/attention. Wash contaminated clothing before using it again.

INHALATION: Remove to open air. In the event of breathing difficulties, get medical advice/attention immediately.

INGESTION: Get medical advice/attention. Induce vomiting only if indicated by the doctor. Never give anything by mouth to an unconscious person, unless authorised by a doctor.

4.2. Most important symptoms and effects, both acute and delayed

ECLULTRA - LumiPRO - Luminol-Enhancer Solution

Specific information on symptoms and effects caused by the product are unknown.

4.3. Indication of any immediate medical attention and special treatment needed

Information not available

SECTION 5. Firefighting measures**5.1. Extinguishing media****SUITABLE EXTINGUISHING EQUIPMENT**

The extinguishing equipment should be of the conventional kind: carbon dioxide, foam, powder and water spray.

UNSUITABLE EXTINGUISHING EQUIPMENT

None in particular.

5.2. Special hazards arising from the substance or mixture**HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE**

Do not breathe combustion products.

5.3. Advice for firefighters**GENERAL INFORMATION**

Use jets of water to cool the containers to prevent product decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewer system. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.

SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS

Normal fire fighting clothing i.e. fire kit (BS EN 469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

SECTION 6. Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Block the leakage if there is no hazard.

Wear suitable protective equipment (including personal protective equipment referred to under Section 8 of the safety data sheet) to prevent any contamination of skin, eyes and personal clothing. These indications apply for both processing staff and those involved in emergency procedures.

ECLULTRA - LumiPRO - Luminol-Enhancer Solution**6.2. Environmental precautions**

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

6.3. Methods and material for containment and cleaning up

Collect the leaked product into a suitable container. If the product is flammable, use explosion-proof equipment. Evaluate the compatibility of the container to be used, by checking section 10. Absorb the remainder with inert absorbent material.

Make sure the leakage site is well aired. Contaminated material should be disposed of in compliance with the provisions set forth in point 13.

6.4. Reference to other sections

Any information on personal protection and disposal is given in sections 8 and 13.

SECTION 7. Handling and storage**7.1. Precautions for safe handling**

Before handling the product, consult all the other sections of this material safety data sheet. Avoid leakage of the product into the environment. Do not eat, drink or smoke during use. Remove any contaminated clothes and personal protective equipment before entering places in which people eat.

7.2. Conditions for safe storage, including any incompatibilities

Store only in the original container. Store the containers sealed, in a well ventilated place, away from direct sunlight. Keep containers away from any incompatible materials, see section 10 for details.

7.3. Specific end use(s)

Information not available

SECTION 8. Exposure controls/personal protection**8.1. Control parameters**

Regulatory References:

DEU	Deutschland	MAK-und BAT-Werte-Liste 2012
ESP	España	INSHT - Límites de exposición profesional para agentes químicos en España 2015
FRA	France	JORF n°0109 du 10 mai 2012 page 8773 texte n° 102

ECLULTRA - LumiPRO - Luminol-Enhancer Solution

GBR	United Kingdom	EH40/2005 Workplace exposure limits
ITA	Italia	Decreto Legislativo 9 Aprile 2008, n.81
PRT	Portugal	Ministério da Economia e do Emprego Consolida as prescrições mínimas em matéria de protecção dos trabalhadores contra os riscos para a segurança e a saúde devido à exposição a agentes químicos no trabalho - Diaro da Republica I 26; 2012-02-06
EU	OEL EU	Directive (EU) 2017/164; Directive 2009/161/EU; Directive 2006/15/EC; Directive 2004/37/EC; Directive 2000/39/EC; Directive 91/322/EEC.
	TLV-ACGIH	ACGIH 2016

ETHANEDIOL**Threshold Limit Value**

Type	Country	TWA/8h		STEL/15min		
		mg/m3	ppm	mg/m3	ppm	
AGW	DEU	26	10	52	20	SKIN
MAK	DEU	26	10	52	20	SKIN
VLA	ESP	52	20	104	40	SKIN
VLEP	FRA	52	20	104	40	SKIN
WEL	GBR	52	20	104	40	
VLEP	ITA	52	20	104	40	SKIN
VLE	PRT	52	20	104	40	SKIN
OEL	EU	52	20	104	40	SKIN
TLV-ACGIH				100 (C)		

Legend:

(C) = CEILING ; INHAL = Inhalable Fraction ; RESP = Respirable Fraction ; THORA = Thoracic Fraction.

8.2. Exposure controls

As the use of adequate technical equipment must always take priority over personal protective equipment, make sure that the workplace is well aired through effective local aspiration.

When choosing personal protective equipment, ask your chemical substance supplier for advice.

Personal protective equipment must be CE marked, showing that it complies with applicable standards.

HAND PROTECTION

Protect hands with category III work gloves (see standard EN 374).

The following should be considered when choosing work glove material: compatibility, degradation, failure time and permeability.

The work gloves' resistance to chemical agents should be checked before use, as it can be unpredictable. The gloves' wear time depends on the duration and type of use.

SKIN PROTECTION

Wear category I professional long-sleeved overalls and safety footwear (see Directive 89/686/EEC and standard EN ISO 20344). Wash body with soap and water after removing protective clothing.

EYE PROTECTION

Wear airtight protective goggles (see standard EN 166).

RESPIRATORY PROTECTION

If the threshold value (e.g. TLV-TWA) is exceeded for the substance or one of the substances present in the product, use a mask with a type A filter whose class (1, 2 or 3) must be chosen according to the limit of use concentration. (see standard EN 14387). In the presence of gases or vapours of various kinds and/or gases or vapours containing particulate (aerosol sprays, fumes, mists, etc.) combined filters are required.

Respiratory protection devices must be used if the technical measures adopted are not suitable for restricting the worker's exposure to the threshold values considered. The protection provided by masks is in any case limited.

ECLULTRA - LumiPRO - Luminol-Enhancer Solution

If the substance considered is odourless or its olfactory threshold is higher than the corresponding TLV-TWA and in the case of an emergency, wear open-circuit compressed air breathing apparatus (in compliance with standard EN 137) or external air-intake breathing apparatus (in compliance with standard EN 138). For a correct choice of respiratory protection device, see standard EN 529.

ENVIRONMENTAL EXPOSURE CONTROLS

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.

SECTION 9. Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	liquid
Colour	From transparent to slightly purplish
Odour	Not available
Odour threshold	Not available
pH	9,65
Melting point / freezing point	Not available
Initial boiling point	Not available
Boiling range	Not available
Flash point	Not available
Evaporation rate	Not available
Flammability (solid, gas)	Not available
Lower inflammability limit	Not available
Upper inflammability limit	Not available
Lower explosive limit	Not available
Upper explosive limit	Not available
Vapour pressure	Not available
Vapour density	Not available
Relative density	Not available
Solubility	Not available
Partition coefficient: n-octanol/water	Not available
Auto-ignition temperature	Not available
Decomposition temperature	Not available
Viscosity	Not available
Explosive properties	Not available
Oxidising properties	Not available

9.2. Other information

Information not available

SECTION 10. Stability and reactivity**10.1. Reactivity**

There are no particular risks of reaction with other substances in normal conditions of use.

ETHANEDIOL

In the air absorbs moisture. Decomposes at temperatures above 200°C/392°F.

10.2. Chemical stability

The product is stable in normal conditions of use and storage.

ECLULTRA - LumiPRO - Luminol-Enhancer Solution**10.3. Possibility of hazardous reactions**

No hazardous reactions are foreseeable in normal conditions of use and storage.

ETHANEDIOL

Risk of explosion on contact with: perchloric acid. May react dangerously with: chlorosulphuric acid, sodium hydroxide, sulphuric acid, phosphorus pentasulphide, chromium (III) oxide, chromyl chloride, potassium perchlorate, potassium dichromate, sodium peroxide, aluminium. Forms explosive mixtures with: air.

10.4. Conditions to avoid

None in particular. However the usual precautions used for chemical products should be respected.

ETHANEDIOL

Avoid exposure to: sources of heat, naked flames.

10.5. Incompatible materials

Information not available

10.6. Hazardous decomposition products**ETHANEDIOL**

May develop: hydroxyacetaldehyde, glyoxal, acetaldehyde, methane, carbon monoxide, hydrogen.

SECTION 11. Toxicological information

In the absence of experimental data for the product itself, health hazards are evaluated according to the properties of the substances it contains, using the criteria specified in the applicable regulation for classification.

It is therefore necessary to take into account the concentration of the individual hazardous substances indicated in section 3, to evaluate the toxicological effects of exposure to the product.

11.1. Information on toxicological effectsMetabolism, toxicokinetics, mechanism of action and other information

Information not available Information not available

Information on likely routes of exposure**ETHANEDIOL**

WORKERS: inhalation; contact with the skin.

POPULATION: inhalation of ambient air; contact with the skin of products containing the substance.

ECLULTRA - LumiPRO - Luminol-Enhancer SolutionDelayed and immediate effects as well as chronic effects from short and long-term exposure**ETHANEDIOL**

Ingestion initially stimulates the central nervous system; later replaced by a phase of depression. There may be kidney damage, with anuria and uremia. Over-exposure symptoms are: vomiting, drowsiness, difficulty in breathing, convulsions. The lethal dose for humans is approx. 1.4 ml/kg.

Interactive effects

Information not available Information not available

ACUTE TOXICITY

LC50 (Inhalation - vapours) of the mixture: LC50 (Inhalation - vapours) of the mixture:

Not classified (no significant component)

LC50 (Inhalation - mists / powders) of the mixture: LC50 (Inhalation - mists / powders) of the mixture:

Not classified (no significant component)

LD50 (Oral) of the mixture: LD50 (Oral) of the mixture:

>2000 mg/kg

LD50 (Dermal) of the mixture: LD50 (Dermal) of the mixture:

Not classified (no significant component)

TRIS

5000 mg/kg rat

LD50 (Oral)

ETHANEDIOL

> 2000 mg/kg Rat

LD50 (Oral)

9530 mg/kg Rabbit

LD50 (Dermal)

SKIN CORROSION / IRRITATION

Does not meet the classification criteria for this hazard class Does not meet the classification criteria for this hazard class

SERIOUS EYE DAMAGE / IRRITATION

Does not meet the classification criteria for this hazard class Does not meet the classification criteria for this hazard class

RESPIRATORY OR SKIN SENSITISATION

May produce an allergic reaction. May produce an allergic reaction.

Contains: Contains:

Sodium 3-(10H-phenothiazin-10-yl)propane-1-sulfonate

GERM CELL MUTAGENICITY

Does not meet the classification criteria for this hazard class Does not meet the classification criteria for this hazard class

CARCINOGENICITY

Does not meet the classification criteria for this hazard class Does not meet the classification criteria for this hazard class

ETHANEDIOL

Available studies have shown no carcinogenic potential. In a carcinogenicity study lasting two years, carried out by the US National Toxicology Program (NTP), in which ethylene glycol was administered in the feed, "no evidence of carcinogenic activity" in male and female B6C3F1 mice was observed (NTP, 1993).

REPRODUCTIVE TOXICITY

Does not meet the classification criteria for this hazard class Does not meet the classification criteria for this hazard class

STOT - SINGLE EXPOSURE

Does not meet the classification criteria for this hazard class Does not meet the classification criteria for this hazard class

STOT - REPEATED EXPOSURE

Does not meet the classification criteria for this hazard class Does not meet the classification criteria for this hazard class

ASPIRATION HAZARD

ECLULTRA - LumiPRO - Luminol-Enhancer Solution

Does not meet the classification criteria for this hazard class Does not meet the classification criteria for this hazard class

SECTION 12. Ecological information

Use this product according to good working practices. Avoid littering. Inform the competent authorities, should the product reach waterways or contaminate soil or vegetation.

12.1. Toxicity

Information not available

12.2. Persistence and degradability

ETHANEDIOL

Solubility in water 1000 - 10000 mg/l

Rapidly biodegradable

12.3. Bioaccumulative potential

ETHANEDIOL

Partition coefficient: n-octanol/water -1,36

12.4. Mobility in soil

Information not available

12.5. Results of PBT and vPvB assessment

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

12.6. Other adverse effects

Information not available

SECTION 13. Disposal considerations**13.1. Waste treatment methods**

Reuse, when possible. Neat product residues should be considered special non-hazardous waste.

Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations.

CONTAMINATED PACKAGING

Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

SECTION 14. Transport information

ECLULTRA - LumiPRO - Luminol-Enhancer Solution

The product is not dangerous under current provisions of the Code of International Carriage of Dangerous Goods by Road (ADR) and by Rail (RID), of the International Maritime Dangerous Goods Code (IMDG), and of the International Air Transport Association (IATA) regulations.

14.1. UN number

Not applicable

14.2. UN proper shipping name

Not applicable

14.3. Transport hazard class(es)

Not applicable

14.4. Packing group

Not applicable

14.5. Environmental hazards

Not applicable

14.6. Special precautions for user

Not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Information not relevant

SECTION 15. Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

Seveso Category - Directive 2012/18/EC: None

ECLULTRA - LumiPRO - Luminol-Enhancer SolutionRestrictions relating to the product or contained substances pursuant to Annex XVII to EC Regulation 1907/2006

None

Substances in Candidate List (Art. 59 REACH)

On the basis of available data, the product does not contain any SVHC in percentage greater than 0,1%.

Substances subject to authorisation (Annex XIV REACH)

None

Substances subject to exportation reporting pursuant to (EC) Reg. 649/2012:

None

Substances subject to the Rotterdam Convention:

None

Substances subject to the Stockholm Convention:

None

Healthcare controls

Information not available

German regulation on the classification of substances hazardous to water (VwVwS 2005)**15.2. Chemical safety assessment**

No chemical safety assessment has been processed for the mixture and the substances it contains.

SECTION 16. Other information

Text of hazard (H) indications mentioned in section 2-3 of the sheet:

Acute Tox. 4	Acute toxicity, category 4
STOT RE 2	Specific target organ toxicity - repeated exposure, category 2
Eye Irrit. 2	Eye irritation, category 2
Skin Irrit. 2	Skin irritation, category 2
Skin Sens. 1	Skin sensitization, category 1
H302	Harmful if swallowed.
H373	May cause damage to organs through prolonged or repeated exposure.
H319	Causes serious eye irritation.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.

ECLULTRA - LumiPRO - Luminol-Enhancer Solution

EUH208 Contains <name of sensitising substance>. May produce an allergic reaction.
EUH210 Safety data sheet available on request.

LEGEND:

- ADR: European Agreement concerning the carriage of Dangerous goods by Road
- CAS NUMBER: Chemical Abstract Service Number
- CE50: Effective concentration (required to induce a 50% effect)
- CE NUMBER: Identifier in ESIS (European archive of existing substances)
- CLP: EC Regulation 1272/2008
- DNEL: Derived No Effect Level
- EmS: Emergency Schedule
- GHS: Globally Harmonized System of classification and labeling of chemicals
- IATA DGR: International Air Transport Association Dangerous Goods Regulation
- IC50: Immobilization Concentration 50%
- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization
- INDEX NUMBER: Identifier in Annex VI of CLP
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PBT: Persistent bioaccumulative and toxic as REACH Regulation
- PEC: Predicted environmental Concentration
- PEL: Predicted exposure level
- PNEC: Predicted no effect concentration
- REACH: EC Regulation 1907/2006
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.
- TWA STEL: Short-term exposure limit
- TWA: Time-weighted average exposure limit
- VOC: Volatile organic Compounds
- vPvB: Very Persistent and very Bioaccumulative as for REACH Regulation
- WGK: Water hazard classes (German).