


## GE-M(KEG) Male stud connector

Male short metric taper thread (DIN 3852-1, type C) / EO 24° cone end



Series	D1	T	D3	L1	L2	L3	L4	S1	S2	Weight g/1 piece	Order code*	PN (bar) <sup>1)</sup>		
												CF	71	MS
LL <sup>2)</sup>	04	M 06×1.0 tap.	2.0	20	16.0	8	26	9	10	5	<b>GE04LLM6X1KEG</b>	100		
	04	M 08×1.0 tap.	3.0	20	16.0	8	26	10	10	7	<b>GE04LLM</b>	100	100	63
	06	M 10×1.0 tap.	4.5	20	14.5	8	26	11	12	9	<b>GE06LLM</b>	100	100	63
	06	M 08×1.0 tap.	3.5	20	14.5	8	26	11	12	9	<b>GE06LLM8X1KEG</b>	100		
	08	M 10×1.0 tap.	6.0	22	16.5	8	28	12	14	10	<b>GE08LLM</b>	100	100	63

<sup>1)</sup> Pressure shown = item deliverable

<sup>2)</sup> LL = very light series

$$\frac{\text{PN (bar)}}{10} = \text{PN (MPa)}$$

Delivery without nut and ring. Information on ordering complete fittings see page 17.

Order code suffixes		
Material	Suffix surface and material	Example
Steel, zinc plated, Cr(VI)-free	CFX	GE06LLMCFX
Stainless Steel	71X	GE06LLM71X
Brass	MSX	GE06LLMMSX

\*Please add the **suffixes** below according to the material/surface required.