

Contactor AC1: 690A/ 690 V Coil DC 72 V x (0,7...1,25) PLC input
 DC 24...110 V auxiliary contacts: 2 NO + 2 NC 3-pole Size S12
 busbar connections coil terminals: screw type screw terminal



Figure similar

| | |
|---|---|
| Product brand name | SIRIUS |
| Product type designation | 3RT14 |
| General technical data | |
| Size of contactor | S12 |
| Product extension | |
| • Auxiliary switch | Yes |
| Surge voltage resistance rated value | 8 kV |
| maximum permissible voltage for safe isolation | |
| • between coil and main contacts acc. to EN 60947-1 | 690 V |
| Protection class IP | |
| • on the front | IP00; IP20 on the front with cover / box terminal |
| • of the terminal | IP00 |
| Shock resistance | |
| • for railway applications acc. to DIN EN 61373 | Category 1, Class B |
| Shock resistance at rectangular impulse | |
| • at DC | 8,5g / 5 ms, 4,2g / 10 ms |

| | |
|---|----------------------------|
| Shock resistance with sine pulse | |
| <ul style="list-style-type: none"> • at DC | 13,4g / 5 ms, 6,5g / 10 ms |
| Mechanical service life (switching cycles) | |
| <ul style="list-style-type: none"> • of contactor typical | 10 000 000 |
| <ul style="list-style-type: none"> • of the contactor with added electronics-compatible auxiliary switch block typical | 5 000 000 |
| <ul style="list-style-type: none"> • of the contactor with added auxiliary switch block typical | 10 000 000 |

Ambient conditions

| | |
|--|----------------|
| Installation altitude at height above sea level | |
| <ul style="list-style-type: none"> • maximum | 2 000 m |
| Ambient temperature | |
| <ul style="list-style-type: none"> • during operation | -40 ... +70 °C |
| <ul style="list-style-type: none"> • during storage | -55 ... +80 °C |

Main circuit

| | |
|---|---------------------|
| Number of poles for main current circuit | 3 |
| Number of NO contacts for main contacts | 3 |
| Number of NC contacts for main contacts | 0 |
| Operating voltage | |
| <ul style="list-style-type: none"> • at AC-3 rated value maximum | 1 000 V |
| Operating current | |
| <ul style="list-style-type: none"> • at AC-1 at 400 V <ul style="list-style-type: none"> — at ambient temperature 40 °C rated value | 690 A |
| <ul style="list-style-type: none"> • at AC-1 <ul style="list-style-type: none"> — up to 690 V at ambient temperature 40 °C rated value | 690 A |
| <ul style="list-style-type: none"> — up to 690 V at ambient temperature 60 °C rated value | 600 A |
| <ul style="list-style-type: none"> • at AC-2 at 400 V rated value | 170 A |
| <ul style="list-style-type: none"> • at AC-3 <ul style="list-style-type: none"> — at 400 V rated value | 170 A |
| <ul style="list-style-type: none"> — at 500 V rated value | 170 A |
| <ul style="list-style-type: none"> — at 690 V rated value | 170 A |
| Connectable conductor cross-section in main circuit at AC-1 | |
| <ul style="list-style-type: none"> • at 60 °C minimum permissible | 480 mm ² |
| <ul style="list-style-type: none"> • at 40 °C minimum permissible | 480 mm ² |
| Operating current | |
| <ul style="list-style-type: none"> • at 1 current path at DC-1 <ul style="list-style-type: none"> — at 24 V rated value | 500 A |
| <ul style="list-style-type: none"> — at 110 V rated value | 33 A |
| <ul style="list-style-type: none"> — at 220 V rated value | 3.8 A |

| | |
|--|---------|
| — at 440 V rated value | 0.9 A |
| — at 600 V rated value | 0.6 A |
| • with 2 current paths in series at DC-1 | |
| — at 24 V rated value | 500 A |
| — at 110 V rated value | 500 A |
| — at 220 V rated value | 500 A |
| — at 440 V rated value | 4 A |
| — at 600 V rated value | 2 A |
| • with 3 current paths in series at DC-1 | |
| — at 24 V rated value | 500 A |
| — at 110 V rated value | 500 A |
| — at 220 V rated value | 500 A |
| — at 440 V rated value | 11 A |
| — at 600 V rated value | 5.2 A |
| Operating current | |
| • at 1 current path at DC-3 at DC-5 | |
| — at 24 V rated value | 500 A |
| — at 110 V rated value | 3 A |
| — at 220 V rated value | 0.6 A |
| — at 440 V rated value | 0.18 A |
| — at 600 V rated value | 0.125 A |
| • with 2 current paths in series at DC-3 at DC-5 | |
| — at 24 V rated value | 500 A |
| — at 110 V rated value | 500 A |
| — at 220 V rated value | 2.5 A |
| — at 440 V rated value | 0.65 A |
| — at 600 V rated value | 0.37 A |
| • with 3 current paths in series at DC-3 at DC-5 | |
| — at 24 V rated value | 500 A |
| — at 110 V rated value | 500 A |
| — at 220 V rated value | 500 A |
| — at 440 V rated value | 1.4 A |
| — at 600 V rated value | 0.75 A |
| Operating power | |
| • at AC-1 | |
| — at 230 V at 60 °C rated value | 245 kW |
| — at 400 V rated value | 430 kW |
| — at 400 V at 60 °C rated value | 430 kW |
| — at 690 V rated value | 740 kW |
| — at 690 V at 60 °C rated value | 740 kW |
| • at AC-2 at 400 V rated value | 90 kW |

| | |
|---|-------------------------------------|
| <ul style="list-style-type: none"> • at AC-3 <ul style="list-style-type: none"> — at 230 V rated value — at 400 V rated value — at 500 V rated value — at 690 V rated value | 160 kW 90 kW 110 kW 160 kW |
| Thermal short-time current limited to 10 s | 4 kA |
| Power loss [W] at AC-3 at 400 V for rated value of the operating current per conductor | 55 W |
| No-load switching frequency <ul style="list-style-type: none"> • at DC | 500 1/h |
| Operating frequency <ul style="list-style-type: none"> • at AC-1 maximum | 500 1/h |
| Operating frequency <ul style="list-style-type: none"> • at DC-1 maximum | 250 1/s |

Ratings for railway applications

| | |
|--|----------------|
| Thermal current (I_{th}) up to 690 V <ul style="list-style-type: none"> • up to 40 °C according to IEC 60077 rated value • up to 70 °C according to IEC 60077 rated value | 690 A 520 A |
|--|----------------|

Control circuit/ Control

| | |
|---|---|
| Type of voltage of the control supply voltage | DC |
| Control supply voltage at DC <ul style="list-style-type: none"> • rated value | 72 V |
| Operating range factor control supply voltage rated value of magnet coil at DC <ul style="list-style-type: none"> • initial value • Full-scale value | 0.7 1.25 |
| Design of the surge suppressor | with varistor |
| Closing power of magnet coil at DC | 800 W |
| Holding power of magnet coil at DC | 3.6 W |
| Closing delay <ul style="list-style-type: none"> • at DC | 60 ... 90 ms |
| Opening delay <ul style="list-style-type: none"> • at DC | 80 ... 100 ms |
| Arcing time | 10 ... 15 ms |
| Control version of the switch operating mechanism | PLC-IN or Standard A1 - A2 (adjustable) |

Auxiliary circuit

| | |
|--|---|
| Number of NC contacts <ul style="list-style-type: none"> • for auxiliary contacts <ul style="list-style-type: none"> — instantaneous contact | 2 |
| Number of NO contacts <ul style="list-style-type: none"> • for auxiliary contacts | |

| | |
|--|---|
| — instantaneous contact | 2 |
| Operating current at AC-12 maximum | 10 A |
| Operating current at AC-15 | |
| • at 230 V rated value | 6 A |
| • at 400 V rated value | 3 A |
| • at 500 V rated value | 2 A |
| Operating current at DC-12 | |
| • at 24 V rated value | 10 A |
| • at 48 V rated value | 6 A |
| • at 60 V rated value | 6 A |
| • at 110 V rated value | 3 A |
| • at 125 V rated value | 2 A |
| • at 220 V rated value | 1 A |
| • at 600 V rated value | 0.15 A |
| Operating current at DC-13 | |
| • at 24 V rated value | 6 A |
| • at 48 V rated value | 2 A |
| • at 60 V rated value | 2 A |
| • at 110 V rated value | 1 A |
| • at 125 V rated value | 0.9 A |
| • at 220 V rated value | 0.3 A |
| • at 600 V rated value | 0.1 A |
| Contact reliability of auxiliary contacts | 1 faulty switching per 100 million (17 V, 1 mA) |

UL/CSA ratings

| | |
|---|-------------|
| Full-load current (FLA) for three-phase AC motor | |
| • at 480 V rated value | 180 A |
| • at 600 V rated value | 192 A |
| Yielded mechanical performance [hp] | |
| • for three-phase AC motor | |
| — at 220/230 V rated value | 75 hp |
| — at 460/480 V rated value | 150 hp |
| — at 575/600 V rated value | 200 hp |
| Contact rating of auxiliary contacts according to UL | A600 / Q600 |

Short-circuit protection

| | |
|---|----------------|
| Design of the fuse link | |
| • for short-circuit protection of the main circuit | |
| — with type of coordination 1 required | Fuse gG: 800 A |
| — with type of assignment 2 required | fuse gR: 710 A |
| • for short-circuit protection of the auxiliary switch required | fuse gG: 10 A |

Installation/ mounting/ dimensions

| | |
|--|---|
| Mounting position | with vertical mounting surface +/-90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back |
| Mounting type | screw fixing |
| <ul style="list-style-type: none"> • Side-by-side mounting | Yes |
| Height | 214 mm |
| Width | 160 mm |
| Depth | 225 mm |
| Required spacing | |
| <ul style="list-style-type: none"> • with side-by-side mounting <ul style="list-style-type: none"> — forwards — Backwards — upwards — downwards — at the side • for grounded parts <ul style="list-style-type: none"> — forwards — Backwards — upwards — at the side — downwards • for live parts <ul style="list-style-type: none"> — forwards — Backwards — upwards — downwards — at the side | 20 mm 0 mm 10 mm 10 mm 10 mm 20 mm 0 mm 10 mm 10 mm 10 mm 10 mm 10 mm 10 mm 10 mm 10 mm |

Connections/Terminals

| | |
|--|--|
| Type of electrical connection | |
| <ul style="list-style-type: none"> • for main current circuit • for auxiliary and control current circuit | screw-type terminals screw-type terminals |
| Type of connectable conductor cross-sections | |
| <ul style="list-style-type: none"> • for main contacts <ul style="list-style-type: none"> — stranded — single or multi-stranded • at AWG conductors for main contacts | 2x (70 ... 240 mm ²) 2x (70 ... 240 mm ²) 2/0 ... 500 kcmil |
| Type of connectable conductor cross-sections | |
| <ul style="list-style-type: none"> • for auxiliary contacts <ul style="list-style-type: none"> — single or multi-stranded — finely stranded with core end processing • at AWG conductors for auxiliary contacts | 2x (0,5 ... 1,5 mm ²), 2x (0,75 ... 2,5 mm ²), max. 2x (0,75 ... 4 mm ²) 2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 2.5 mm ²) 2x (20 ... 16), 2x (18 ... 14), 1x 12 |

Safety related data

Product function

- Mirror contact acc. to IEC 60947-4-1
- positively driven operation acc. to IEC 60947-5-1

Yes
No

Certificates/approvals

| | | |
|---------------------------------|--|----------------------------------|
| General Product Approval | Functional Safety/Safety of Machinery | Declaration of Conformity |
|---------------------------------|--|----------------------------------|



[Type Examination Certificate](#)



| | | | |
|--------------------------|--------------------------|--------------|----------------|
| Test Certificates | Marine / Shipping | other | Railway |
|--------------------------|--------------------------|--------------|----------------|

[Special Test Certificate](#)



[Confirmation](#)

[Miscellaneous](#)

[Vibration and Shock](#)

[Confirmation](#)

Further information**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RT1476-6XJ46-0LA2>

Cax online generator




<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT1476-6XJ46-0LA2>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RT1476-6XJ46-0LA2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT1476-6XJ46-0LA2&lang=en





last modified:

10/13/2017