



Figure similar

SITOP PSE200U SELECTIVITY MODULE 3A
 SITOP PSE200U 3 A SELECTIVITY MODULE 4-CHANNEL INPUT:
 24 V DC; OUTPUT: 24 V DC/3 A PER EACH CHANNEL OUTPUT
 CURRENT ADJUSTABLE 0.5-3

Input	
Type of the power supply network	Controlled DC voltage
Supply voltage / for DC / Rated value	24 V
Input voltage / for DC	22 ... 30
Oversoltage overload capability	35 V
Input current / at rated input voltage 24 V / Rated value	12 A
Output	
Voltage curve / at output	controlled DC voltage
Formula for output voltage	$V_{in} - \text{approx. } 0.2 \text{ V}$
Relative overall tolerance / of the voltage / Note	In accordance with the supplying input voltage
Number of outputs	4
Output current / up to 60 °C / per output / Rated value	3 A
Adjustable response value current / of the current-dependent overload release	0.5 ... 3
Type of response value setting	via potentiometer
Product property / parallel switching of outputs	No
Type of outputs connection	Simultaneous connection of all channels after power up of the supply voltage > 20 V, delay time of 25 ms, 100 ms or adjustable "load optimised" via DIP switch for sequential connection
Efficiency	
Efficiency in percent	97 %
Active power loss / at rated output current / at rated output current / typical	9 W

Switch-off characteristic per output	
Switching characteristic	
<ul style="list-style-type: none"> • of the excess current • of the current limitation • of the immediate switch-off 	I _{out} = 1.0 ... 1.5 x set value, switch-off after approx. 5 s I _{out} = 1.5 x set value, switch-off not before typ. 100 ms I _{out} > set value and V _{in} < 20 V, switch-off after approx. 0.5 ms
Design of the reset device/resetting mechanism	via sensor per output
Remote reset function	Non-electrically isolated 24 V input (signal level "high" at > 15 V)

Protection and monitoring	
Overload protection type / for cables	5 A per output (not accessible)
Display version / for normal operation	Three-color LED per output: green LED for "Output switched through"; yellow LED for "Output switched off manually"; red LED for "Output switched off due to overcurrent"
Design of the switching contact / for signaling function	Common signal contact (changeover contact, rating 0.1 A/24 V DC)

Safety	
Galvanic isolation / between input and output at switch-off	No
Operating resource protection class	Class III
Certificate of suitability	
<ul style="list-style-type: none"> • CE marking • UL approval • as approval for USA 	Yes Yes UL-Recognized (UL 2367) File E328600; cULus-Listed (UL 508, CSA C22.2 No. 107.1) File E197259
Standard	
<ul style="list-style-type: none"> • for safety • for explosion protection 	according to EN 60950-1 and EN 50178 IECEx (IEC 60079-0, -15); ATEX (EN 60079-0, -15); cCSAus (CSA C22.2 No. 213, No. 60079, ANSI/ISA 12.12.01, UL 60079)
Certificate of suitability	
<ul style="list-style-type: none"> • relating to ATEX • Shipbuilding approval 	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cCSAus Class I, Div. 2, Group ABCD, T4 Yes
Shipbuilding approval	GL, ABS
Protection class IP	IP20

EMC	
Standard	
<ul style="list-style-type: none"> • for emitted interference • for interference immunity 	EN 55022 Class B EN 61000-6-2

Operating data	
Ambient temperature	
<ul style="list-style-type: none"> • during operation — Note • during transport 	0 ... 60 with natural convection -40 ... +85

- during storage

-40 ... +85

Mechanics

Type of electrical connection	screw-type terminals
<ul style="list-style-type: none"> • at input 	+24 V: 2 screw terminals for 0.5 ... 10 mm ² ; 0 V: 2 screw terminals for 0.5 ... 4 mm ²
<ul style="list-style-type: none"> • at output 	Output 1 ... 4: 1 screw terminal each for 0.5 ... 4 mm ²
<ul style="list-style-type: none"> • for signaling contact 	3 screw terminals for 0.5 ... 4 mm ²
<ul style="list-style-type: none"> • for auxiliary contacts 	Remote reset: 1 screw terminal for 0.5 ... 4 mm ²
Width / of the enclosure	72 mm
Height / of the enclosure	80 mm
Depth / of the enclosure	72 mm
Installation width	72 mm
Mounting height	180 mm
Net weight	0.2 kg
Mounting type	Snaps onto DIN rail EN 60715 35x7.5/15
Mechanical accessories	Device identification label 20 mm × 7 mm, pastel-turquoise 3RT1900-1SB20
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)