

Ascent 150 II Round Aluminium Reflector

ASCENT 150 II 3900 4K STD EM
2059370



Product features

- The ASCENT 150 II 3900 4K STD EM is a high efficient downlight luminaire , Colour rendering index Ra >80, Colour temperature: 4000K Neutral White, Class II, Protection rating IP44/IK03



PRODUCT OVERVIEW

Product name	ASCENT 150 II 3900 4K STD EM
Technology	LED
Cap/Base	N/A
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Internal
General application	Hospitality, Office, Retail
ETIM Class	EC001744
Warranty	5 years
Fixture luminous flux (lm)	3900
Luminaire efficacy (lm/W)	126
LOR (%)	100
Colour temperature (K)	4000
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Colour Consistency (SDCM)	3
Beam Angle (°)	80
Glare control	< 23
Photobiological Risk Group	RG0
Luminous flux (emergency) (lm)	421
Total power consumption (W)	31
Electrical protection	Class II
Control gear type	Electronic ballast
Dimmable	No
Dimming method	N/A
Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP44/20
IK rating	IK03
Product EAN number	5025768593705

Ascent 150 II Round Aluminium Reflector

ASCENT 150 II 3900 4K STD EM
2059370

DATA TABLE

General data

Product name	ASCENT 150 II 3900 4K STD EM
Technology	LED
Cap/Base	N/A
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Internal
General application	Hospitality, Office, Retail
Operating temperature range (°C)	25°C...+25°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
Warranty	5 years

Optical data

Fixture luminous flux (lm)	3900
Luminaire efficacy (lm/W)	126
LOR (%)	100
Colour temperature (K)	4000
Correlated colour temperature range (K)	4000 - 4000
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Colour Consistency (SDCM)	3
Adjustable chromaticity	N
Beam Angle (°)	80
Distribution type	Diffuse
Glare control	< 23
Photobiological Risk Group	RG0
Luminous flux (emergency) (lm)	421
Emergency duration (h)	3

Electrical data

Total power consumption (W)	31
Mains voltage (V)	220-240V
Lamp power factor	1
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	20
Electrical protection	Class II
Control gear type	Electronic ballast
Transformer required	Yes
Dimmable	No
Dimming method	N/A
Drive current (mA)	1050
Inrush Current (A)	10
Inrush Duration (µs)	100
Glow Wire Test (°C)	650

Ascent 150 II Round Aluminium Reflector

ASCENT 150 II 3900 4K STD EM
2059370

Energy Efficiency Class (A->G) of contained light source	B
Nominal Frequency (Hz)	50/60/HF
Max. Luminaires per 10A C Breaker	35
Max. Luminaires per 13A C Breaker	50
Max. Luminaires per 16A C Breaker	65
Max. Luminaires per 20A C Breaker	75
Max. Luminaires per 10A B Breaker	35
Max. Luminaires per 13A B Breaker	50
Max. Luminaires per 16A B Breaker	65
Max. Luminaires per 20A B Breaker	75

Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	100000
Lifespan L90 B10	55000

Physical data

Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP44/20
IK rating	IK03
Diffuser finish	Transparent
Diffuser material	PC Polycarbonate
Reflector finish	Other
Nominal Product Width (mm)	189
Nominal Product Height (mm)	107
Nominal Product Diameter (mm)	189
Cutout Dimensions (W x L in mm or Diameter in mm)	176
Weight (kg)	1.78
Recessed Depth (mm)	120

Packaging





Single packaging type	Carton
Product EAN number	5025768593705
Packaging single length / height (cm)	30.0
Packaging single width (cm)	30.0
Packaging single depth (cm)	20.0
DUN14 (outer)	05025768593705
Units per outer package	1
Packaging outer length / height (cm)	30.0
Packaging outer width (cm)	30.0
Packaging outer depth (cm)	20.0

Safety data

Optimal operating condition (°C)	25-25
----------------------------------	-------

Ascent 150 II Round Aluminium Reflector *ASCENT 150 II 3900 4K STD EM* 2059370

PHOTOMETRY



TECHNICAL DRAWINGS

