



FLACHRUNDKOPF MIT GERILLEM NIETDORN DOMED HEAD WITH GROOVED MANDREL TÊTE PLATE CLOU CANNELÉ











Edelstahl A2 [1.4301]
Stainless steel A2 [AISI 304]
Acier inox A2 [1.4301]

Edelstahl A2 [1.4301]
Stainless steel A2 [AISI 304]
Acier inox A2 [1.4301]











Ø 4,8 mm

D1 = 4,8 + / - 0,09 mm
D2 = 10,0 + 0 / - 1,0 mm
k = 2,2 + / - 0,25 mm
d = 3,0 mm (Ref.)
P = ≥ 27,0 mm
L = + / - 0,99 mm
 4,9 - 5,1 mm

	F max		CODE					
4,8 x 10,5 mm	20,0 mm	1,8 - 6,9 mm	77705 04810	5700 N	4400 N	445 N	250	2500
4,8 x 14,5 mm	27,0 mm	1,8 - 11,0 mm	77705 04814				250	2500

Ø 6,4 mm

D1 = 6,4 + 0 / - 0,11 mm
D2 = 13,5 + 0 / - 1,5 mm
k = 3,0 + / - 0,4 mm
d = 4,0 mm (Ref.)
P = ≥ 31,0 mm
L = + / - 0,99 mm
 6,6 - 6,9 mm

	F max		CODE					
6,4 x 14,5 mm	27,0 mm	2,0 - 9,5 mm	77705 06414	10500 N	8200 N	1112 N	250	2500 ²⁾
6,4 x 20,5 mm	37,0 mm	2,0 - 15,9 mm	77705 06420				250	2500 ²⁾

¹⁾ typische Werte typical values valeurs moyennes

²⁾ **Auf Anfrage:** Deutsches Institut für Bautechnik (DIBt, German Authority in Civil Engineering) Approval No. Z-14.1-4 Attachment 2-23

Technische Änderungen vorbehalten Subject to technical modifications Sous réserve de modifications (techniques)