

3-jaw chuck ZG

With base plate



Application:

For use in drilling and milling machines.

Execution:

- Cast body
- Clamped with socket wrench
- To achieve the requisite clamping force, the lathe chuck must be lubricated regularly.
- To achieve the requisite clamping force, the lathe chuck must be lubricated regularly.
- For spare jaws see no. 22389-22416 onwards.

Delivery:

1 scroll chuck with 1 set of drilling jaws, 1 set of turning jaws, ref. no. 070 with reversible jaws, 1 clamping pin



Art. no.	22370 020
Brand	RÖHM
Manufacturer Part Number	127858
Outer diameter	200 mm
Max. clamping range diameter	200 mm
Clearance hole	55 mm
Base plate diameter	280 mm
Length	14 mm
Groove width	252 mm
Height with jaws	133 mm
Base plate height	27 mm
Weight	20.6 kg
Gross Weight	27.200 kg
Product Group	203