

Electronic micrometer

With V-anvil

Mitutoyo

Application:

For measuring cutting tools, e.g. screw taps, cutters, reamers.

Execution:

- measuring faces made of hardened steel
- ABS function
- HOLD (measured value storage)
- Preset function

Advantage:

- Long battery life, approx. 2.4 years

Delivery:

Includes box, setting standard, battery



Art. no.	32017 480
Brand	MITUTOYO
Manufacturer Part Number	314-351-30
Display	Digital
Min./max. length measuring range in inches	0.05-0.6 in
Digit increment	0.00005 in
Measuring arrangement	60°- Throat, Truncated cone (60°)
IP protection class	IP 40
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Digit height	7.5 mm
Functions	ABS function, Hold-function (AE lock), Preset function, Automatic switch-off
Min./max. measurement force	3-8 N
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Measuring spindle increments	0.75 mm
Calibration Group	D, E
Gross Weight	0.470 kg
Product Group	3MA

EAN

494636869563 1