


### High Efficiency LED, Ø 5 mm Tinted Non-Diffused Package



### DESCRIPTION

The TLH.52.. series was developed for standard applications like general indicating and lighting purposes.

It is housed in a 5 mm tinted non-diffused plastic package. The small viewing angle of these devices provides a high brightness.

Several selection types with different luminous intensities are offered. All LEDs are categorized in luminous intensity groups. The green and yellow LEDs are categorized additionally in wavelength groups.

That allows users to assemble LEDs with uniform appearance.

### PRODUCT GROUP AND PACKAGE DATA

- Product group: LED
- Package: 5 mm
- · Product series: standard
- Angle of half intensity: ± 14°

### FEATURES

- Choice of three bright colors
- Standard T-1¾ package
- Small mechanical tolerances
- · Suitable for DC and high peak current
- Small viewing angle
- Luminous intensity categorized
- · Yellow and green color categorized
- TLH.52.. with stand-offs
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

#### **APPLICATIONS**

- Status lights
- Off/on indicator
- Background illumination
- Readout lights
- Maintenance lights
- Legend light

PARTS TABLE														
PART	COLOR	LUMINOUS INTENSITY (mcd)		at I <sub>F</sub>		VELENGTH (nm)		at I <sub>F</sub>	FORWARD VOLTAGE (V)		at I <sub>F</sub>	TECHNOLOGY		
		MIN.	TYP.	MAX.	(mA)	MIN.	TYP.	MAX.	(mA) -	MIN.	TYP.	MAX.	(mA)	
TLHR5200	Red	10	50	-	10	612	-	625	10	-	2	3	20	GaAsP on GaP
TLHR5201	Red	16	60	-	10	612	-	625	10	-	2	3	20	GaAsP on GaP
TLHR5205	Red	25	70	-	10	612	-	625	10	-	2	3	20	GaAsP on GaP
TLHY5200	Yellow	10	50	-	10	581	-	594	10	-	2	3	20	GaAsP on GaP
TLHG5200	Green	16	40	-	10	562	-	575	10	-	2	3	20	GaP on GaP
TLHG5201	Green	25	45	-	10	562	-	575	10	-	2	3	20	GaP on GaP
TLHG5201-AS12Z	Green	25	45	-	10	562	-	575	10	-	2	3	20	GaP on GaP
TLHG5205	Green	40	50	-	10	562	-	575	10	-	2	3	20	GaP on GaP
TLHG5205-AS21	Green	40	50	-	10	562	-	575	10	-	2	3	20	GaP on GaP

Pb-free e3

RoHS COMPLIANT HALOGEN FREE GREEN (5-2008)



www.vishay.com

**Vishay Semiconductors** 

<b>ABSOLUTE MAXIMUM RATINGS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified) <b>TLHR520. TLHY520.</b> , <b>TLHG520.</b>						
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT		
Reverse voltage		V <sub>R</sub>	6	V		
DC forward current	T <sub>amb</sub> ≤ 65 °C	I <sub>F</sub>	30	mA		
Surge forward current	t <sub>p</sub> ≤ 10 μs	I <sub>FSM</sub>	1	А		
Power dissipation	T <sub>amb</sub> ≤ 65 °C	Pv	100	mW		
Junction temperature		Tj	100	°C		
Operating temperature range		T <sub>amb</sub>	-40 to +100	°C		
Storage temperature range		T <sub>stg</sub>	-55 to +100	°C		
Soldering temperature	$t \le 5$ s, 2 mm from body	T <sub>sd</sub>	260	°C		
Thermal resistance junction/ambient		R <sub>thJA</sub>	350	K/W		

# **OPTICAL AND ELECTRICAL CHARACTERISTICS** ( $T_{amb} = 25 \text{ °C}$ , unless otherwise specified) **TLHR520.**, **RED**

PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
		TLHR5200	Iv	10	50	-	mcd
Luminous intensity <sup>(1)</sup>	I <sub>F</sub> = 10 mA	TLHR5201	I <sub>V</sub>	16	60	-	mcd
		TLHR5205	I <sub>V</sub>	25	70	-	mcd
Dominant wavelength	I <sub>F</sub> = 10 mA		$\lambda_d$	612	-	625	nm
Peak wavelength	I <sub>F</sub> = 10 mA		λρ	-	635	-	nm
Angle of half intensity	I <sub>F</sub> = 10 mA		φ	-	± 14	-	deg
Forward voltage	I <sub>F</sub> = 20 mA		V <sub>F</sub>	-	2	3	V
Reverse voltage	I <sub>R</sub> = 10 μA		V <sub>R</sub>	6	15	-	V
Junction capacitance	V <sub>R</sub> = 0 V, f = 1 MHz		Cj	-	50	-	pF

#### Note

<sup>(1)</sup> In one packing unit  $I_{Vmin}/I_{Vmax} \le 0.5$ 

### **OPTICAL AND ELECTRICAL CHARACTERISTICS** (T<sub>amb</sub> = 25 °C, unless otherwise specified) **TLHY520.. YELLOW**

PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity <sup>(1)</sup>	I <sub>F</sub> = 10 mA	TLHY5200	Ι <sub>V</sub>	10	50	-	mcd
Dominant wavelength	I <sub>F</sub> = 10 mA		$\lambda_d$	581	-	594	nm
Peak wavelength	I <sub>F</sub> = 10 mA		λρ	-	585	-	nm
Angle of half intensity	I <sub>F</sub> = 10 mA		φ	-	± 14	-	deg
Forward voltage	I <sub>F</sub> = 20 mA		V <sub>F</sub>	-	2	3	V
Reverse voltage	I <sub>R</sub> = 10 μA		V <sub>R</sub>	6	15	-	V
Junction capacitance	V <sub>R</sub> = 0 V, f = 1 MHz		Cj	-	50	-	pF

#### Note

<sup>(1)</sup> In one packing unit  $I_{Vmin}/I_{Vmax.} \le 0.5$ 

<b>OPTICAL AND ELECTRICAL CHARACTERISTICS</b> ( $T_{amb} = 25 \text{ °C}$ , unless otherwise specified) <b>TLHG520., GREEN</b>							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
		TLHG5200	Ι <sub>V</sub>	16	40	-	mcd
Luminous intensity <sup>(1)</sup>	I <sub>F</sub> = 10 mA	TLHG5201	Iv	25	45	-	mcd
		TLHG5205	Ι <sub>V</sub>	40	50	-	mcd
Dominant wavelength	I <sub>F</sub> = 10 mA		λ <sub>d</sub>	562	-	575	nm
Peak wavelength	I <sub>F</sub> = 10 mA		λρ	-	565	-	nm
Angle of half intensity	I <sub>F</sub> = 10 mA		φ	-	± 14	-	deg
Forward voltage	I <sub>F</sub> = 20 mA		V <sub>F</sub>	-	2	3	V
Reverse voltage	I <sub>R</sub> = 10 μA		V <sub>R</sub>	6	15	-	V
Junction capacitance	V <sub>R</sub> = 0 V, f = 1 MHz		Cj	-	50	-	pF

#### Note

 $^{(1)}$  In one packing unit  $I_{Vmin.}/I_{Vmax.} \leq 0.5$ 

Rev. 1.9, 16-Mar-15



www.vishay.com

**Vishay Semiconductors** 

### **TYPICAL CHARACTERISTICS** ( $T_{amb} = 25 \text{ °C}$ , unless otherwise specified)




Fig. 1 - Forward Current vs. Ambient Temperature




Fig. 2 - Forward Current vs. Pulse Length




Fig. 3 - Relative Luminous Intensity vs. Angular Displacement




Fig. 4 - Forward Current vs. Forward Voltage




Fig. 5 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 6 - Relative Luminous. Intensity vs. Forward Current/Duty Cycle

Rev. 1.9, 16-Mar-15

3 For technical questions, contact: <u>LED@vishav.com</u> Document Number: 83011

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



**Vishay Semiconductors** 




Fig. 7 - Relative Luminous Intensity vs. Forward Current




Fig. 8 - Relative Intensity vs. Wavelength




Fig. 9 - Forward Current vs. Forward Voltage




Fig. 10 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 12 - Relative Luminous Intensity vs. Forward Current

4

For technical questions, contact: <u>LED@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>






Fig. 13 - Relative Intensity vs. Wavelength




Fig. 14 - Forward Current vs. Forward Voltage




Fig. 15 - Relative Luminous Intensity vs. Ambient Temperature

**Vishay Semiconductors** 




Fig. 16 - Specific Luminous Intensity vs. Forward Current




Fig. 17 - Relative Luminous Intensity vs. Forward Current




Fig. 18 - Relative Intensity vs. Wavelength

Rev. 1.9, 16-Mar-15

5

Document Number: 83011


For technical questions, contact: <u>LED@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>




### TLHR520., TLHY520., TLHG520.

### **Vishay Semiconductors**

### **PACKAGE DIMENSIONS** in millimeters








technical drawings according to DIN specifications

6.544-5258.01-4 Issue: 5; 19.05.09 96 12119


### REEL



AS12 = cathode leaves tape first

AS21 = anode leaves tape first

TAPE



6 For technical questions, contact: LED@vishay.com



### TLHR520., TLHY520., TLHG520.

**Vishay Semiconductors** 

### AMMOPACK





Fig. 21 - Tape Direction

#### Note

• The new nomenclature for ammopack is e.g. ASZ only, without suffix for the LED orientation. The carton box has to be turned to the desired position: "+" for anode first, or "-" for cathode first. AS12Z and AS21Z are still valid for already existing types, BUT NOT FOR NEW DESIGN.

### TAPE DIMENSIONS in millimeters



Option	Dim. "H" ± 0.5 mm
AS	17.3



Vishay

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.