# Surface Mount Rectifier multicomp

RoHS

**Compliant** 



## **Features**

- **Glass Passivated Die Construction**
- Ideally Suited for Automatic Assembly
- Low Forward Voltage Drop
- Low Power Loss
- . Ultra-Fast Recovery Time
- Plastic Case Material has UL Flammability Classification Rating 94V-0

## **Mechanical Data**

Case	: SMB/DO-214AA, Molded Plastic
Terminals	: Solder Plated, Solderable per MIL-STD-750, Method 2026
Polarity	: Cathode Band or Cathode Notch
Forward Current	: 1 Amperes
Marking	: Type Number
Weight	: 0.093 grams(approx)

## **Maximum Ratings and Electrical Characteristics**

Ratings at 25°C ambient temperature unless otherwise specified.

Characteristics	Symbol	MURS120+	MURS160+	Units
Peak Repetitive Reverse Voltage	Vrrm	200	600	V
Working Peak Reverse Voltage	Vrms	200	600	
DC Blocking Voltage	VR	200	600	
RMS Reverse Voltage	VR(RMS)	140	420	
Average Rectified Output Current @ T∟ = 90°C	lo		1	
Non-Repetitive Peak Forward Surge Current, 8.3ms Single Half Sine-Wave Superimposed on Rated Load (JEDEC Method)	Ігѕм	40	35	А
Forword Voltage @I⊧ = 1A	VF	0.875	1.25	V
Maximum Reverse Current at Rated $T_A = 25^{\circ}C$ DC Blocking Voltage $T_A = 125^{\circ}C$	IR	2 250	5 250	μA
Reverse Recovery Time (Note1)	trr	25	50	ns
Typical Junction Capacitance(Note2)	CJ	13		pF
Typical Thermal Resistance(Note3)	Reja	15		W/°C
Operating Temperature Range	TJ	-55 to +150		°C
Storage Temperature Range	Tstg			

### Note:

- 1. Measured With IF=0.5A, IR=1.0A, Irr=0.25A
- 2. Measured at 1 MHz and applied reverse voltage of 4V DC.
- 3. Mounted on P.C. Board with 8mm<sup>2</sup> land area.
- 4. The typical data above is for reference only

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



# **Rating and Characteristic Curves**





FIG.3-TYPICAL FORWARD CHARACTERISTICS








FIG.4-TYPIACL JUNCTION CAPACITANCE



PERCENT OF RATED PEAK REVERSE VOLTAGE,%






Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

# multicomp PRO

## **Dimensions:**

### SMB/DO-214AA



Dimensions : Inches (Millimetres)

## **Part Number Table**

Description	Part Number	
Rectifiers, 1A 200V SMB	MURS120+	
Rectifiers, 1A 600V SMB	MURS160+	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

