


Start Waterproof LED G3 fixed output

START Waterproof Single 1500 IP65 4000lm 840 QC
0067973



Product features

- Start Waterproof, integrated LED weatherproof luminaire, with UV stabilized flat diffuser and linear prisms designed to achieve uniform lit appearance, optimise light output and to reduce glare, 301 stainless steel diffuser clips and fixing brackets for surface mounting. Polycarbonate housing, Polycarbonate diffuser, 3950 lm, 35 W, 120 lm/W, 4000 K, drive current 350 mA, Non dimmable with quick connector, CRI80, IP65, IK08, Class I, nominal average life (h):50000, 1578 mm x 84 mm x 75 mm ,energy class: A++ A+ A, D-mark



PRODUCT OVERVIEW

Product name	START Waterproof Single 1500 IP65 4000lm 840 QC
Technology	LED
Housing	PC Polycarbonate
Fixture rating	Enclosed
General application	Logistics & Industry
ETIM Class	EC002892
Warranty	5 years
Fixture luminous flux (lm)	3950
Luminaire efficacy (lm/W)	113
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Glare control	< 25
Photobiological Risk Group	RG0
Total power consumption (W)	35
Electrical protection	Class I
Dimmable	No
Dimming method	N/A
Housing colour	Grey
IP rating	IP65
IK rating	IK08
Product EAN number	5410288679730

DATA TABLE

General data

Product name	START Waterproof Single 1500 IP65 4000lm 840 QC
Technology	LED
Housing	PC Polycarbonate
Fixture rating	Enclosed
General application	Logistics & Industry
Operating temperature range (°C)	-10°C...+40°C

Start Waterproof LED G3 fixed output

START Waterproof Single 1500 IP65 4000lm 840 QC
0067973

Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
Warranty	5 years

Optical data

Fixture luminous flux (lm)	3950
Luminaire efficacy (lm/W)	113
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Glare control	< 25
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	35
Mains voltage (V)	220-240V
Lamp power factor	0.95
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	20
Electrical protection	Class I
Dimmable	No
Dimming method	N/A
Drive current (mA)	350
Glow Wire Test (°C)	850
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	20
Max. Luminaires per 13A C Breaker	30
Max. Luminaires per 16A C Breaker	40
Max. Luminaires per 20A C Breaker	50
Max. Luminaires per 10A B Breaker	16
Max. Luminaires per 13A B Breaker	24
Max. Luminaires per 16A B Breaker	32
Max. Luminaires per 20A B Breaker	40

Lifetime data

Lifespan L70 B50	60000
Lifespan L70 B20	60000
Lifespan L70 B10	60000
Lifespan L80 B50	60000
Lifespan L80 B20	60000
Lifespan L80 B10	60000
Lifespan L90 B50	59000
Lifespan L90 B20	53000
Lifespan L90 B10	50000

Physical data

Housing colour	Grey
IP rating	IP65
IK rating	IK08

Start Waterproof LED G3 fixed output

START Waterproof Single 1500 IP65 4000lm 840 QC
0067973

Diffuser finish	Transparent
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	1578
Nominal Product Width (mm)	84
Nominal Product Height (mm)	75
Weight (kg)	2.1


Packaging

Single packaging type	Carton
Product EAN number	5410288679730
Packaging single length / height (cm)	167.2
Packaging single width (cm)	8.8
Packaging single depth (cm)	8.4
DUN14 (outer)	05410288679730
Units per outer package	1
Packaging outer length / height (cm)	167.2
Packaging outer width (cm)	8.8
Packaging outer depth (cm)	8.4

Safety data

Optimal operating condition (°C)	-10-40
Dry applications use only	No

PHOTOMETRY



Distance [m]	Cone diameter [m]	E(0°)	E(C90)	E(C0)	Illuminance [lx]
0.5	1.29 1.37	5438	543*	540	659
1.0	2.78 2.73	1361	543*	135	162
1.5	4.17 4.10	593	543*	50	62
2.0	5.57 5.47	339	543*	34	38
2.5	6.96 6.83	217	543*	22	22
3.0	8.35 8.20	151	543*	15	15

Distance [m] Cone diameter [m] Illuminance [lx]
 C0 - C180 (Half beam angle: 107.6°)
 C90 - C270 (Half beam angle: 108.6°)

TECHNICAL DRAWINGS

