

Thread boring bar, internal, left

for holding thread turning inserts for internal machining

ATORN®

Application


For female thread machining for thread turning inserts.

Version

- precision-engineered steel support, burnished and hardened, with 1.5° pitch angle

Advantage

- top-quality and wear-resistant steel support with high-strength clamping screw
- precision-engineered insert seat provides extremely precise threads and excellent finish quality



Art. No.	17747 172
ISO name	SIR/L 0025 R16
Suitable for indexable insert size	16
Min. bore diameter	29 mm
Cutting edge diameter	25 mm
Shaft diameter	25 mm
Length	200 mm
Programming size	16.2 mm
Coolant supply	External
Tool design	Left

EAN-Code

4050293208900