



DECLARACIÓN DE PRESTACIONES

fischer innovative solutions

no 0031 – ES

1. Código de identificación única del producto tipo: **fischer nail anchor FNA II**

2. Usos previstos:

producto	Uso/s previsto/s
anclaje metálico para fijación de sistemas ligeros en hormigón	para aplicación en sistemas redundantes para la fijación y/o anclaje de elementos constructivos, tales como falsos techos ligeros, además de instalaciones en hormigón, Véase el apéndice, especialmente los anexos B 1 - B 2

3. Fabricante: **fischerwerke GmbH & Co. KG, Klaus-Fischer-Straße 1, 72178 Waldachtal, Germany**

4. Representante autorizado: --

5. Sistemas de evaluación y verificación de la constancia de las prestaciones (EVCP): **2+**

6a. Norma armonizada: ---

Organismos notificados: ---

6b. Documento de evaluación europeo: **ETAG 001; 2016-04**Evaluación técnica europea: **ETA-06/0175; 2016-10-28**Organismo de evaluación técnica: **DIBt**Organismos notificados: **1343 – MPA Darmstadt**

7. Prestaciones declaradas:

Resistencia mecánica y estabilidad (BWR 1)

indicación esencial	Prestaciones
valores característicos	Ver anexo, especialmente anexo C 1

protección contra incendios (BWR 2)

indicación esencial	Prestaciones
Reacción al fuego	el anclaje cumple con las exigencias de la clase A1.
resistencia al fuego	Ver anexo, especialmente anexo C 2

Seguridad durante el uso (BWR 4)

indicación esencial	Prestaciones
valores característicos para solicitudes a tracción y a cortante	Ver anexo, especialmente anexo C 1

8. Documentación técnica adecuada o documentación técnica específica: ---

Las prestaciones del producto identificado anteriormente son conformes con el conjunto de prestaciones declaradas. La presente declaración de prestaciones se emite, de conformidad con el Reglamento (UE) no 305/2011, bajo la sola responsabilidad del fabricante arriba identificado.

Firmado por y en nombre del fabricante por:

Andreas Bucher, Dipl.-Ing.

Wolfgang Hengesbach, Dipl.-Ing., Dipl.-Wirtsch.-Ing.

Tumlingen, 2016-11-04

- Este DoP ha sido redactado en varios idiomas. En caso de disputa acerca de la interpretación siempre prevalecerá la versión en inglés.

- el anexo contiene información voluntaria y complementaria en inglés, que va más allá de las exigencias legales.

Specific Part**1 Technical description of the product**

The fischer nail anchor FNA II is an anchor made of galvanised steel, stainless steel (marking "A4") or high corrosion resistant steel (marking "C") which is pushed into a drilled hole and expanded by loading.

The product description is given in Annex A.

2 Specification of the intended use in accordance with the applicable European Assessment Document

The performances given in Section 3 are only valid if the anchor is used in compliance with the specifications and conditions given in Annex B.

The verifications and assessment methods on which this European Technical Assessment is based lead to the assumption of a working life of the anchor of at least 50 years. The indications given on the working life cannot be interpreted as a guarantee given by the producer, but are to be regarded only as a means for choosing the right products in relation to the expected economically reasonable working life of the works.

3 Performance of the product and references to the methods used for its assessment**3.1 Mechanical resistance and stability (BWR 1)**

The essential characteristics regarding Mechanical resistance and stability are included under the Basic Works Requirement Safety in use.

3.2 Safety in case of fire (BWR 2)

Essential characteristic	Performance
Reaction to fire	Anchorages satisfy requirements for Class A1
Resistance to fire	See Annex C 2

3.3 Safety in use (BWR 4)

Essential characteristic	Performance
Characteristic resistance for all load directions	See Annex C 1


4 Assessment and verification of constancy of performance (AVCP) system applied, with reference to its legal base

In accordance with guideline for European technical approval ETAG 001, April 2013 used as European Assessment Document (EAD) according to Article 66 Paragraph 3 of Regulation (EU) No 305/2011 the applicable European legal act is: [97/161/EC].

The system to be applied is: 2+

**Only for multiple use for non-structural applications according to
ETAG 001 Part 6 Annex 1**


Design types:




FNA II 6x25/..
FNA II 6x30/..




FNA II 6x25/.. RB
FNA II 6x30/.. RB



FNA II 6x25 M6/..
FNA II 6x30 M6/..




FNA II 6x25 M8/..
FNA II 6x30 M8/..



FNA II 6x25 OE
FNA II 6x30 OE

Intended use:




Additional marking only galvanised steel for $h_{ef} = 25$ mm (centring, bar or points)

fischer nail anchor FNA II

Product description

Product and intended use

Annex A 1

Marking:**Nail head**


Marking at **X**: "O" for $h_{ef} = 25$ mm
and "I" for $h_{ef} = 30$ mm;

Marking at **Y**: t_{fix}

Marking at **Z**: "A4" or "C" (stainless steel)

Expansion sleeve (or bolt)

e.g.:




For stainless steel additional marking "A4" or "C"


Marking-Codes for Y:

	A	Q	T	N	P	B	L	H	U
t_{fix}	5	10	15	20	25	30	35	40	45
	D	V	S	W	X	E	M	Z	K
t_{fix}	50	55	60	65	70	75	80	85	90
	(A)	F	(B)	(D)	(E)	G	J		
t_{fix}	95	100	105	110	115	120	125		

At $t_{fix} > 125$ mm the corresponding figure is marked.

Shaft (threaded bolt)


Marking e.g.: 6/10
thread size/thickness of the fixture



Marking e.g.: 8/10
thread size /thickness of the fixture
Exception: 8/5 no marking

Table A1: Materials

Designation	Material: Galvanized steel
Cone Bolt	Cold form steel or free cutting steel (zinc plated) Nominal steel tensile strength: $f_{uk} \leq 1000$ N/mm ²
Expansion sleeve	Cold strip, EN 10139:2013 (zinc plated)
Designation	Material: A4 (stainless steel)
Cone Bolt	Stainless steel EN 100882: 2014 Nominal steel tensile strength: $f_{uk} \leq 1000$ N/mm ²
Expansion sleeve	Stainless steel EN 10088: 2014
Designation	Material: C (high corrosion resistant steel)
Cone Bolt	High corrosion resistant steel EN 10088: 2014 Nominal steel tensile strength: $f_{uk} \leq 1000$ N/mm ²
Expansion sleeve	Stainless steel EN 10088: 2014

**fischer nail anchor FNA II**

Product description
Marking and materials

Annex A 2

Specifications of intended use

Anchorage subject to:

- Static and quasi-static loads: All types and all embedment depths
- Fasteners are only to be used for multiple use for non-structural applications, according to ETAG 001 Part 6, Edition January 2011
- Fire exposure: only for concrete C20/25 to C50/60

Base materials:

- Reinforced and unreinforced normal weight concrete according to EN 206-1: 2000
- Strength classes C12/15 to C50/60 according to EN 206-1: 2000
- Uncracked and cracked concrete: All types and all embedment depths

Use conditions (Environmental conditions):

- Structures subject to dry internal conditions (gvz, A4, C) with $h_{ef} \geq 25$ mm
- Structures subject to permanently damp internal condition, if no other particular aggressive conditions exist (A4, C) with $h_{ef} \geq 25$ mm
- Structures subject to external atmospheric exposure including industrial and marine environment, if no particular aggressive conditions exist (A4, C) with $h_{ef} \geq 30$ mm
- Structures subject to external atmospheric exposure and to permanently damp internal condition, if other particular aggressive conditions exist (C) with $h_{ef} \geq 30$ mm

Note: Particular aggressive conditions are e.g. permanent, alternating immersion in seawater or the splash zone of seawater, chloride atmosphere of indoor swimming pools or atmosphere with extreme chemical pollution(e.g. in desulphurization plants or road tunnels where de-icing materials are used.)

Design:

- Anchorages have to be designed under the responsibility of an engineer experienced in anchorages and concrete work
- Verifiable calculation notes and drawings have to be prepared taking account of the loads to be anchored. The position of the anchor is indicated on the design drawings (e.g. position of the anchor relative to reinforcement or to supports, etc.)
- Anchorages under static or quasi-static actions have to be designed in accordance with:
 - ETAG 001, Annex C, design method C, Edition August 2010 or
 - CEN/TS 1992-4: 2009, design method C
- Anchorages under fire exposure have to be designed in accordance with:
 - EOTA Technical Report TR 020, Edition May 2004
 - CEN/TS 1992-4: 2009
 - It must be ensured that local spalling of the concrete cover does not occur


Installation:

- Anchor installation carried out by appropriately qualified personnel and under the supervision of the person responsible for technical matters of the site
- Create drill hole with hammer drill and clean the hole
- Anchor installation such that the effective anchorage depth is complied with. This compliance is ensured, if the admissible thickness of the fixture is kept. For the anchor type FNA II 6 x h_{ef} OE the loop has to sit direct at the concrete surface.
- In case of aborted hole: New hole must be drilled at a minimum distance of twice the depth of the aborted hole or closer, if the hole is filled with a high strength mortar and only if the hole is not in the direction of the oblique tensile or shear load



fischer nail anchor FNA II	Annex B 1
Intended Use Specifications	

Table B1: Installation parameters


Effective embedment depth	$h_{\text{ef}} \geq$	[mm]	25	30
Nominal drill bit diameter	d_0	[mm]	6	
Cutting diameter of drill bit	$d_{\text{cut}} \leq$	[mm]	6,4	
Depth of drill hole	$h_0 \geq$	[mm]	31	36
Diameter of clearance hole in the fixture for all FNA II except for M8 and OE	$d_f \leq$	[mm]		7
Diameter of clearance hole in the fixture for M8	$d_f \leq$	[mm]		9
Maximum torque moment (only threaded types)	max. T_{inst}	[Nm]		4
Minimum thickness of member	h_{min}	[mm]		80
Maximum thickness of fixture	max. t_{fix}	[mm]		400

**Installation instruction:**


Push through installation



Pre-positioned installation



or



or

fischer nail anchor FNA II**Intended Use**

Installation parameters

Annex B 2

Table C1: Characteristic resistance of a fixing point¹⁾ for all load directions

Type of anchor	FNA II 6x25/..	FNA II 6x25 M6/.. FNA II 6x25 M8/..	FNA II 6x25 OE	FNA II 6x30 OE	FNA II 6x30 M6/.. FNA II 6x30 M8/..
Material	galv.	galv., A4, C			
Effective anchorage depth	$h_{ef} \geq [mm]$	25			30 ⁴⁾
Installation safety factor	$\gamma_2 [-]$		1,0		
Characteristic bending moment	$M_{Rk,s}^0$ ³⁾ [Nm]	10,7	9,2	13,2	9,2
Partial safety factor	$\gamma_{Ms} [-]$		1,25		
Maximum load for normal spacing - and edge distances					
Characteristic spacing between fixing points ¹⁾	$s_{cr} \geq [mm]$		200		
Minimum spacing within a fixing point ¹⁾	$s_{min} \geq [mm]$		50		
Characteristic resistance F_{Rk} C20/25 to C50/60 (C12/15)	$c_{cr}^{2)} \geq 100$ $c_{cr}^{2)} \geq 50$ [kN]	3,0 (2,5) 2,35 (1,9)	1,5	5,0 (4,0) 2,35 (1,9)	
Reduced loads for reduced spacing - and corresponding edge distances					
Characteristic spacing between fixing points ¹⁾	$s_{cr} \geq [mm]$		100		
Minimum spacing within a fixing point ¹⁾	$s_{min} \geq [mm]$		50		
Characteristic resistance F_{Rk} C20/25 to C50/60 (C12/15)	$c_{cr}^{2)} \geq 200$ $c_{cr}^{2)} \geq 50$ [kN]	3,0 (2,5) 1,7 (1,2)	1,5 1,5 (1,2)	5,0 (4,0) 1,7 (1,2)	
Reduced loads for minimum spacing - and edge distance					
Characteristic spacing between fixing points ¹⁾	$s_{cr} \geq [mm]$		100		
Minimum spacing within a fixing point ¹⁾	$s_{min} \geq [mm]$		40		
Characteristic resistance F_{Rk} C20/25 to C50/60 (C12/15)	$c_{cr} \geq 40$ [kN]			1,30 (0,85)	

¹⁾ A fixing point is defined as a single anchor or a group of 2 or 4 anchors²⁾ Intermediate values for c may be calculated by linear interpolation³⁾ Characteristic bending moment $M_{Rk,s}^0$ according equation (5.5), ETAG 001, Annex C⁴⁾ Exception see B1 – use conditions – point 2**fischer nail anchor FNA II****Performances**

Characteristic resistance

Annex C 1

Table C2: Characteristic resistance under fire exposure in concrete C20/25 to C50/60

Fire resistance class for all load directions for $h_{ef} = 25$ mm							
Type of anchor	Spacing	Edge distance	Effective anchorage depth	Characteristic resistance $F_{Rk,fi}$ [kN]			
	$s_{cr,fi} \geq [mm]$	$c_{cr,fi} \geq [mm]$	$h_{ef} \geq [mm]$	R 30	R 60	R 90	R 120
FNA II 6x25/..galv.	100	50	25	0,6	0,6	0,5	0,3
FNA II 6x25 M6/.. galv. FNA II 6x25 M8/.. galv.					0,35	0,3	
FNA II 6x25 OE galv.				0,3	0,2		0,1

Fire resistance class for all load directions for $h_{ef} = 30$ mm							
Type of anchor	Spacing	Edge distance	Effective anchorage depth	Characteristic resistance $F_{Rk,fi}$ [kN]			
	$s_{cr,fi} \geq [mm]$	$c_{cr,fi} \geq [mm]$	$h_{ef} \geq [mm]$	R 30	R 60	R 90	R 120
FNA II 6x30/..galv.	120	60	30	0,9	0,8	0,5	0,3
		50			0,6		
FNA II 6x30 M6/.. galv. FNA II 6x30 M8/.. galv.		120 100			0,35	0,3	
FNA II 6x30/..A4/C	120	60	30	0,9			0,7
	100	50		0,6			0,5
FNA II 6x30 M6/..A4/C FNA II 6x30 M8/..A4/C	120 100	60 50		0,9			0,7
FNA II 6x30 OE A4/C	100	50	30	0,6			0,5
				0,3	0,2		0,1

Fire resistance class for all load directions for $h_{ef} = 30+5^{1)}$ mm							
Type of anchor	Spacing	Edge distance	Effective anchorage depth	Characteristic resistance $F_{Rk,fi}$ [kN]			
	$s_{cr,fi} \geq [mm]$	$c_{cr,fi} \geq [mm]$	$h_{ef} \geq [mm]$	R 30	R 60	R 90	R 120
FNA II 6x30/..A4/C	140	70	30+5 ¹⁾	1,3		1,0	0,7
FNA II 6x30 M6/..A4/C FNA II 6x30 M8/..A4/C		50		0,7			0,6

¹⁾ The effective anchorage depth $h_{ef} = 30 + 5$ mm is reached by setting the anchor FNA 6x30/... 5 mm deeper with an anchor that is 5 mm longer than required for the actual thickness of the fixture.

In case of fire attack from more than one side, the edge distance shall be ≥ 300 mm

fischer nail anchor FNA II

Performances

Characteristic resistance under fire exposure

Annex C 2