



FEATURES

- Efficiency up to 86%
- DIP Package with Industry Standard Pinout
- Wide 2:1 Input Range
- Operating Temperature Range -40°C to $+85^{\circ}\text{C}$
- Isolation Voltage 1500VDC
- Short Circuit Protection
- CSA60950-1 Safety Approval
- 3 Years Product Warranty



The DP06S/D series are miniature, DIP Package, isolated 6W DC/DC converters with 1,500VDC isolation. It offers short circuit protection and allows a wide operating temperature range of -40°C to $+85^{\circ}\text{C}$. These isolated DC/DC converters are the latest offering from a world leader in power systems technology and manufacturing — Delta Electronics, Inc. With creative design technology and optimization of component placement, these converters possess outstanding electrical and thermal performance, as well as extremely high reliability under highly stressful operating conditions.

Model List

Model Number	Input Voltage (Range)	Output Voltage	Output Current		Input Current		Reflected Ripple Current	Max. capacitive Load	Efficiency (typ.)
			Max.	Min.	@Max. Load	@No Load			@Max. Load
		VDC	mA	mA	mA(typ.)	mA(typ.)			%
DP06S1203A	12 (9 ~ 18)	3.3	1200	60	429	20	25	6800	77
DP06S1205A		5	1000	50	514				81
DP06S1212A		12	500	25	595				84
DP06D1212A		± 12	± 250	± 12.5	595			1000*	84
DP06D1215A		± 15	± 200	± 10	595				84
DP06S2403A	24 (18 ~ 36)	3.3	1200	60	209	5	15	6800	79
DP06S2405A		5	1000	50	251				83
DP06S2412A		12	500	25	291				86
DP06D2412A		± 12	± 250	± 12.5	291			1000*	86
DP06D2415A		± 15	± 200	± 10	291				86

* For each output

Input Characteristics

Parameter	Model	Min.	Typ.	Max.	Unit
Input Surge Voltage (1 sec. max.)	12V Input Models	-0.7	---	25	VDC
	24V Input Models	-0.7	---	50	
Start-Up Voltage	12V Input Models	4.5	6	8	
	24V Input Models	8	12	16	
Under Voltage Shutdown	12V Input Models	---	---	8	
	24V Input Models	---	---	16	
Reverse Polarity Input Current	All Models	---	---	1	A
Short Circuit Input Power		---	1000	3000	mW
Internal Power Dissipation		---	---	2500	mW
Conducted EMI (with suffix E only)		Compliance to EN 55022, class A and FCC part 15, class A			

Output Characteristics

Parameter	Conditions	Min.	Typ.	Max.	Unit
Output Voltage Accuracy		---	±0.5	±1.0	%
Output Voltage Balance	Dual Output, Balanced Loads	---	±0.5	±2.0	%
Line Regulation	Vin=Min. to Max.	---	±0.1	±0.3	%
Load Regulation	Io=20% to 100%	---	±0.3	±1.0	%
Ripple & Noise (20MHz)		---	50	75	mV _{P-P}
Ripple & Noise (20MHz)	Over Line, Load & Temp.	---	---	100	mV _{P-P}
Ripple & Noise (20MHz)		---	---	15	mV _{rms}
Transient Recovery Time	25% Load Step Change	---	150	300	μs
Transient Response Deviation		---	±2	±6	%
Temperature Coefficient		---	±0.01	±0.02	%/°C
Over Load Protection	Foldback	120	150	---	%
Short Circuit Protection	Continuous				

General Characteristics

Parameter	Conditions	Min.	Typ.	Max.	Unit
I/O Isolation Voltage (rated)	60 Seconds	1500	---	---	VDC
I/O Isolation Resistance	500 VDC	1000	---	---	MΩ
I/O Isolation Capacitance	100KHz, 1V	---	380	500	pF
Switching Frequency		---	300	---	KHz
MTBF (calculated)	MIL-HDBK-217F@25°C, Ground Benign	1,000,000	---	---	Hours
Safety Approvals	UL/cUL 60950-1 recognition(CSA certificate), IEC/EN 60950-1(CB-scheme)				


Recommended Input Fuse

12V Input Models	24V Input Models
1500mA Slow-Blow Type	700mA Slow-Blow Type

Environmental Characteristics

Parameter	Conditions	Min.	Max.	Unit
Operating Temperature Range (with Derating)	Ambient	-40	+85	°C
Case Temperature		---	+90	°C
Storage Temperature Range		-50	+125	°C
Humidity (non condensing)		---	95	% rel. H
Cooling	Free-Air convection			
Lead Temperature (1.5mm from case for 10Sec.)		---	260	°C

Power Derating Curve



Notes

- Specifications typical at $T_a = +25^\circ\text{C}$, resistive load, nominal input voltage and rated output current unless otherwise noted.
- Transient recovery time is measured to within 1% error band for a step change in output load of 75% to 100%.
- Ripple & Noise measurement bandwidth is 0-20MHz.
- These power converters require a minimum output loading to maintain specified regulation, operation under no-load conditions will not damage these modules; however they may not meet all specifications listed.
- All DC/DC converters should be externally fused at the front end for protection.
- To order the converter with input filter meeting EN55022, Class A, add suffix E (e.g. Dp06s1203E) to order code.
- Specifications subject to change without notice.

Mechanical Drawing

Mechanical Dimensions

The figure displays two views of a rectangular electronic module: a top view and a bottom view.

Top View: Shows the module's profile with a total height of 10.2 mm [0.40]. It features four pins of diameter $\varnothing 0.50$ mm [0.02]. The distance from the top edge to the pin centerline is 4.1 mm [0.16].

Bottom View: Shows the module's footprint with a total width of 31.8 mm [1.25] and a total height of 20.3 mm [0.80]. Pin locations are defined by the following dimensions (all in mm [inches]):

- Pin 2 to Pin 3: 2.54 [0.10]
- Pin 3 to Pin 9: 15.24 [0.60]
- Pin 9 to Pin 11: 5.08 [0.20]
- Pin 11 to Pin 14: 4.5 [0.18]
- Pin 14 to Pin 16: 2.54 [0.10]
- Pin 16 to Pin 22: 15.24 [0.60]
- Pin 22 to Pin 23: 2.54 [0.10]

The text "Bottom View" is centered on the drawing.

Pin Connections

Pin	Single Output	Dual Output
2	-Vin	-Vin
3	-Vin	-Vin
9	No Pin	Common
11	NC	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin	+Vin
23	+Vin	+Vin

NC: No Connection

- ▶ All dimensions in mm (inches)
- ▶ Tolerance: X.X±0.25 (X.XX±0.01)
X.XX±0.13 (X.XXX±0.005)
- ▶ Pin diameter ⇔ 0.5 ±0.05 (0.02±0.002)

Physical Outline

Case Size : 31.8x20.3x10.2mm (1.25x0.80x0.40 Inches)

Case Material : Non-Conductive Black Plastic (flammability to UL 94V-0 rated)

Weight : 16.9g



Part Numbering System						
D	P	06	S	12	05	A
Form factor	Family series	Watt	Number of Outputs	Input Voltage	Output Voltage	Option Code
D-DIP	A~Z	01:1W	S - Single	03:3.3V	03:3.3V	A - Std. Functions
P-SIP		02:2W	D- Dual	05: 5V	05: 5V	
S-SMD		03:3W		12:12V	12:12V	
		04:4W		24: 24V	15: 15V	
		06:6W		48:48V	24: 24V	

WARRANTY

Delta offers a three(3) years limited warranty. Complete warranty information is listed on our web site or is available upon request from Delta.

Information furnished by Delta is believed to be accurate and reliable. However, no responsibility is assumed by Delta for its use, nor for any infringements of patents or other rights of third parties, which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Delta. Delta reserves the right to revise these specifications at any time, without notice.