



Part Number: 70007E

DataTuff® PROFINET Cat 5e Type B - Moderate Flexing Cable

Product Description

DataTuff PROFINET Type B, Cat 5e, 100Mb/s, Quad, AWG 22(7), Stranded, Foil+ 85% Braid, PVC jacket, UL AWM 2464

Technical Specifications

Product Overview

Physical Characteristics (Overall)
Conductor
AWG Stranding Material Construction n x D No. of Conductors
22 Stranded TC - Tinned Copper 7x0.25 mm 4
Conductor Count: 4
Total Number of Pairs: 2
Conductor Size: 22 AWG

Material	Nominal Diameter	Diameter +/- Tolerance
PO - Polyolefin	1.55 mm	0.05 mm

Color Chart

Number	Color
Quad 1	White & Blue & Yellow & Orange

Inner Jacket Material

Material	Nominal Diameter
PVC Bedding	4.1 mm

Outer Shield Material

Type	Material	Thickness of Foil	Min. Coverage [%]
Tape	Aluminum/Polyester	50 μm	
Braid	TC - Tinned Copper		85 %

Outer Jacket Material

Material	Color	Nominal Diameter	Diameter +/- Tolerance
PVC (Oil resistant)	Green (RAL 6018)	6.5 mm	0.2 mm

Construction and Dimensions

Cabling



Electrical Characteristics

Conductor DCR



Shielding:	Foil + Braid(s)

Impedance

Frequency [MHz]	Nominal Characteristic Impedance	Nominal Characteristic Tolerance
1 - 100	100 Ohm	15 Ohm

Delay

Max. Delay	Nominal Velocity of Propagation (VP) [%]
530 ns/100m	68 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. ACRF (ELFEXT) [dB]	Min. SRL (Structural Return Loss)
1 MHz	2.1 dB/100m	65.3 dB	64 dB	
4 MHz	4.1 dB/100m	56.3 dB	52 dB	23 dB
10 MHz	6.5 dB/100m	50.3 dB	44 dB	25 dB
16 MHz	8.3 dB/100m	47.2 dB	40 dB	25 dB
31.25 MHz	11.7 dB/100m	42.9 dB	34 dB	23.6 dB
62.5 MHz	17 dB/100m	38.4 dB	28 dB	21.5 dB
100 MHz	22 dB/100m	35.3 dB	24 dB	20.1 dB

Transfer Impedance

Frequency [MHz]	Transfer Impedance
10 Mhz	Max. 10 mOhm/m

Voltage

Voltage Rating [V]

Temperature Range

Installation Temp Range:	-5°C To +60°C
Storage Temp Range:	-40°C To +80°C
Operating Temp Range:	-40°C To +80°C

Mechanical Characteristics

Oil Resistance:	IEC 60811-2-1

Standards

ISO/IEC Compliance:	ISO/IEC 11801 Ed. 2.2:2002/A2:2010/C1:2011
CPR Euroclass:	Eca
Data Category:	Category 5e

Applicable Environmental and Other Programs

EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01

Flammability, LS0H, Toxicity Testing

ISO/IEC Flammability:	IEC 60332-1-2	

Part Number

Variants

Item #	Color
70007E.011000	Green
70007E.011525	Green
70007E.01305	Green
70007E.01500	Green
70007E.01B100	Green
Patent:	

History

Revision Number:	4

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.