



**Part no.: 50111227**  
**KB M12A-8P-USB-3000**  
**Connection cable**




Figure can vary

## Contents

- Technical data
- Electrical connection

## Technical data

<b>Basic data</b>	
Suitable for interface	USB

<b>Connection</b>	
<b>Connection 1</b>	
Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	8 -pin
Encoding	A-coded
Design	Axial

<b>Connection 2</b>	
Type of connection	USB
Connector type	USB 2.0 Standard-A

<b>Cable properties</b>	
Number of conductors	4 Piece(s)
Sheathing color	Gray
Shielded	Yes
Cable design	Interconnection cable
Cable diameter (external)	5 mm
Cable length	3,000 mm
Sheathing material	PUR

<b>Classification</b>	
Customs tariff number	85444290
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855

## Electrical connection

<b>Connection 1</b>	
Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	8 -pin
Encoding	A-coded
Design	Axial

<b>Connection 2</b>	
Type of connection	USB
Connector type	USB 2.0 Standard-A