

Transverse drive shell end mill arbor DIN 6357 (face mill arbor)

With enlarged collar diameter, ISO-7388-1

ATORN[®]

Version

- Alloyed case-hardening steel, tensile strength in the core min. 950 N/mm²
- Internal coolant supply
- Case-hardened HRc 60 ± 2 (HV 700 ± 50), hardness depth 0.8 mm ± 0.2 mm
- max. concentricity < 0.005 mm
- Taper angle tolerance quality < AT3 in accordance with DIN 7187 and DIN 2080

Delivery

includes key blocks and cutter retaining screw



Art. no.	23162 196
Tool holding device	SK 50
Form	AD
Mandrel diameter	22 mm
Tap length	19 mm
Projecting length	130 mm
Outer diameter	48 mm
Balancing quality	G 2.5 at 25 rpm
Coolant supply	Internal axial

EAN-Code

4050293712308