

Sheet metal punches, Tristar

12.5 to 63 mm



Application:

For punching holes in sheet metal.

Execution:

- Sheet hole-punch system with slug splitter for standard steel S235
- Burr-free hole punching
- Actuated using a wrench, hydraulic punch or cordless compact punch
- When actuated with a wrench, draw bolts with ball bearings must be used

Advantage:

- The sheet does not jam in the centre thanks to the triple partition

Delivery:

Stamp and die – screw or tension bolt has to be ordered separately



Art. no.	53829 283
Brand	ALFRA
Manufacturer Part Number	01777
Diameter	28.3 mm
Suitable for max. sheet metal thickness	2 mm
Suitable for pipe (PG)	PG 21
Screw diameter	9.5 mm
Screw length	50 mm
Gross Weight	0.169 kg
Product Group	554

EAN

4030266122716

