



1	0833	2	0833	3	0000	4		5		6		7		8
SUPERSEDES 9280 723 05100 0833/000 p.190-1 Of 09/10/2012		UV LAMP HPM 15 (MnNi)				9280 723 05100 0833/000			17/09/2014					
REF. : UV-328	DOCUMENTATION	UNIT mm	PROJ. EUROP 	2 SH	SH 190-1	10	1:1	A4						
NAME : J.P. CHARLIER	VALIDATION : A. PICHARD		DR. FISCHER Europe											
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.														

PRODUCT REQUIREMENT SHEET

See LV-75-034



ELECTRICAL DATA
(with the specified ballast)

	Measuring Point	Value	Unit	Tolerance
Lamp Wattage	0h	1950	W	Nom
Lamp Voltage	0h	245	V	± 15
Lamp Current	0h	9	A	Nom
Power Density	0h	NA	W/cm	Nom
Ignition Supply Voltage	0h	350	V	min
Ignition Time	0h	20	s	Max
Warm-Up Time		4	min	Max
Re-Ignition Time		10	min	Max

UV RADIATION
(with the specified ballast)

	Measuring Point	Value	Unit	Tolerance
UV-A (315-400 nm)	0h	NA	µW/cm ²	± 10%
UV-B (280-315 nm)	0h	850 *	µW/cm ²	± 10%
UV-C (200-280 nm)	0h	NA	µW/cm ²	± 10%
DIAZO (350-460 nm)	0h	4100	µW/cm ²	± 10%
UV Maintenance	750h	80	%	min
Doping	Gallium			
Quartz Tube	Ozone Free			

GENERAL SPECIFICATIONS
(in operating conditions)

	Value	Unit	Tolerance
Bulb Temperature	750 950	°C	min Max
Pinch Temperature	350	°C	Max
Lamp Position	Horizontal		

BALLAST DESCRIPTION

Ballast Reference	BHL 2000L18		
Ballast Power (indicative)	2000 W	Supply Voltage	380 V
Supply Wave Form	Sine wave	Frequency	50 Hz
Ignitor Reference	380 MZN 4000	Capacitor Reference	30+30 µF

1	0833	2	0833	3	0000	4	m : xxx g	5		6		7		8	
SUPERSEDES :		UV LAMP						9280 723 05100		20/06/2017					
9280 723 05100		HPM 15 (MnNi)						0833/000							
0833/000 p190-2															
Of 12/07/2016															
REF. :	PDM UV-423	DOCUMENTATION	UNIT mm	PROJ EUROP	2 SH	SH	190-2	10	A4						
NOM :	J.P. CHARLIER	VALIDATION : A. PICHARD				DR. FISCHER Europe									
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.															